



Point of Sale Display for TREDUX

• TREDUX-Display

Features and Benefits

With TREDUX HellermannTyton has set a new standard in heat shrink tubing:

TREDUX offers a complete range of thin, medium and thick wall tubing cut into 1m-length. Securely packed in display boxes, they can be removed individually for occasional use in smaller quantities.

The shrink ratio 3:1 conforms very well to highly variable substrate dimensions and replaces many differently sized tubing solutions by fitting almost any heat shrink task. This reduces stock cost, and saves space.

All tubing are labeled with an EAN barcode. This allows for a fast and error-free billing as well as the complete registration of the stock.

The carton can be opened easily at the pre-perforated top and provides a clear presentation of the heatshrink range.



The TREDUX display.



The TREDUX Mixpack.

Technical Table

Article-No.	Type	Supplied Ø D	Recov. Ø d	Wall (WT)	Pack Cont. (piece/1m)	Colour
Proposed content for a TREDUX display						
TREDUX thin wall						
319-00150	TREDUX-1.5/0.5	1.5	0.5	0.50	20	Black (BK)
319-00300	TREDUX-3/1	3.0	1.0	0.60	20	Black (BK)
319-00300	TREDUX-3/1	3.0	1.0	0.60	20	Black (BK)
319-00600	TREDUX-6/2	6.0	2.0	0.70	15	Black (BK)
319-00600	TREDUX-6/2	6.0	2.0	0.70	15	Black (BK)
319-01200	TREDUX-12/4	12.0	4.0	0.85	10	Black (BK)
319-01200	TREDUX-12/4	12.0	4.0	0.85	10	Black (BK)
319-01200	TREDUX-12/4	12.0	4.0	0.85	10	Black (BK)
319-01200	TREDUX-12/4	12.0	4.0	0.85	10	Black (BK)
319-02400	TREDUX-24/8	24.0	8.0	1.20	5	Black (BK)
319-00307	TREDUX-3/1-GNYE	3.0	1.0	0.60	20	Green-Yellow (GNYE)
319-00607	TREDUX-6/2-GNYE	6.0	2.0	0.70	15	Green-Yellow (GNYE)
319-01207	TREDUX-12/4-GNYE	12.0	4.0	0.85	10	Green-Yellow (GNYE)
TREDUX MA47, Medium wall adhesive lined						
323-50120	TREDUX-MA47-12/3	12.0	3.0	2.0	6	Black (BK)
323-50120	TREDUX-MA47-12/3	12.0	3.0	2.0	6	Black (BK)
323-50190	TREDUX-MA47-19/6	19.0	6.0	2.5	10	Black (BK)
323-50300	TREDUX-MA47-30/8	30.0	8.0	2.5	6	Black (BK)
323-50300	TREDUX-MA47-30/8	30.0	8.0	2.5	6	Black (BK)
323-50400	TREDUX-MA47-40/12	40.0	12.0	2.5	4	Black (BK)
TREDUX HA47, Thick wall adhesive lined						
321-50130	TREDUX-HA47-13/4	13.0	4.0	2.4	6	Black (BK)
321-50130	TREDUX-HA47-13/4	13.0	4.0	2.4	6	Black (BK)
321-50190	TREDUX-HA47-19/6	19.0	6.0	2.7	10	Black (BK)
321-50330	TREDUX-HA47-33/8	33.0	8.0	3.2	5	Black (BK)
321-50450	TREDUX-HA47-45/12	45.0	12.0	4.1	4	Black (BK)
319-30000	TREDUX-Display	-	-	-	1	Blue (BU)

All dimensions in mm. Subject to technical changes.