



### Self-laminating labels, manual marking

- RiteOn, Starter Pack, Material 1401 dispenser

#### Features and Benefits

These self-laminating labels provide simple and rapid identification for low volume installation and rework. The coloured text field gives a good contrast to the cable for extra clarity.

The RiteOn protective laminating clear tail ensures optimal protection against humidity, dirt and debris and mechanical abrasion.

Write your text in the marker window of the dispenser, dispense the label, place the shaded area with the text onto the cable surface and wrap the clear 'tail' around the cable.

#### • RiteOn Starter Pack

The Starter Pack contains all you need to start work identifying your wires:

- 1 x RiteOn dispenser
- 1 x R202 reel of 150 self laminating labels for cable diameters ranging from 4mm to 11mm
- 1 x T82S-BK black indelible ink marker pen




The RiteOn starter pack gets you started right away.

Material Data	
Material	<b>Type 1401, Vinyl</b>
Colour	<b>White (WH)</b>
Operating Temperature	<b>-40 °C to +80 °C</b>
Curing Temperature	<b>From +10 °C</b>
Adhesive	<b>Acrylic</b>
Chem. Material Properties	<b>Resistant to water, alcohol, most oils, greases, fuel, aliphatic solvents, weak acids, salts and alkalis.</b>



Manual Marking



#### Technical Table

Article-No.	Type	Colour	Bundle Ø min.	Bundle Ø max.	Width (W)	Height (H)	Height (H2)	Pack Cont.
Starter pack and filled dispensers								
550-14010	<b>SPRO200-1401-WH</b>	White (WH)	6.10	12.10	19.05	12.70	50.80	150
550-14011	<b>RO201-1401-WH</b>	White (WH)	4.00	8.10	12.70	12.70	38.10	200
550-14012	<b>RO202-1401-WH</b>	White (WH)	6.10	12.10	19.05	12.70	50.80	150
550-14013	<b>RO203-1401-WH</b>	White (WH)	9.10	18.20	19.05	25.40	76.20	100
Refill packs								
550-14014	<b>RO201REF-1401-WH</b>	White (WH)	4.00	8.10	12.70	12.70	38.10	200
550-11401	<b>RO202REF-1401-WH</b>	White (WH)	6.10	12.10	19.05	12.70	50.80	150
550-71401	<b>RO203REF-1401-WH</b>	White (WH)	9.10	18.20	19.05	25.40	76.20	100
Marker pens T82								
500-50820	<b>T82S-BK</b>	Black (BK)	-	-	-	-	-	2
500-50822	<b>T82R-RD</b>	Red (RD)	-	-	-	-	-	2

All dimensions in mm. Subject to technical changes.