



Data sheet | Item number: 756-5301/060-015

Sensor/actuator cable; fitted on one end (with free end); 5-pole; M12 socket, straight; one free cable end; 1.5 m



www.wago.com/756-5301/060-015





| Pin 1 ... 5: 0,34 mm ² | |
|-----------------------------------|-------------|
| 1) | braun (+) |
| 2) | weiß (Ö) |
| 3) | blau (-) |
| 4) | schwarz (S) |
| 5) | grau |
| ----- Schirm | |

Item description

Short description:

- PUR, halogen-free
- Suitable for drag chains
- Good resistance to microbes, hydrolysis, oil, chemicals and UV radiation.
- Good chemical resistance.
- Cable used: UL listed

Data

Technical Data

| | |
|---|-----------------------|
| Connection type | M12 socket - free end |
| No. of poles | 5 |
| Anschlusspunkt geschirmt | yes |
| Leitungsanschlussrichtung zur Steckrichtung | 0° |
| Steckgesichtskodierung Leitung/Adapter 1 1 | A coded |
| Cable length | 1.5 m |
| Operating voltage | AC/DC 250 V |
| Operating current | 4 A |
| Rated surge voltage | 1,5 kV |
| Resistance of conductor | < 57 Ω/km |

Mechanical data

| | |
|-------------------------------|--|
| Bending cycles | 2 |
| Schleppkettentauglichkeit | yes |
| Color of sheathed cable | black |
| Durchmesser der Mantelleitung | 6.3 ... 6.7 mm |
| Sheath material | Polyurethane (OPUR), halogen-free per DIN VDE 0472 Part 815, flame resistant per IEC 332-2, self-extinguishing |
| Halogen-free | Yes |
| Housing material | Polyurethan (PUR) |
| Contact material | CuSn |
| Contact plating | CuNi/Au |
| Tightening torque | 1 Nm |
| Weight | 110 g |

Environmental Requirements

| | |
|--------------------------------------|--------------------|
| Umgebungstemperatur (Betrieb) bewegt | -25 ... +90 °C |
| Umgebungstemperatur (Betrieb) ruhend | -50 ... +90 °C |
| Degree of protection | IP67 |
| Degree of pollution (5) | 3 acc. to VDE 0110 |

Commercial data

| | |
|--------------------|---------------|
| Country of origin | HU |
| GTIN | 4045454724696 |
| Customs Tariff No. | 85444290900 |

Downloads

Documentation

System Description

| | | |
|--------------------------------------|-------------|----------|
| IP67 Cables and Pluggable Connectors | Jun 6, 2017 | Download |
| | | 434.4 kB |

Subject to changes.