

# Shrink sleeve - WMS 19,1 (EX30)RL - 0800326

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Shrink sleeve, Roll, white, Unlabeled, Can be labeled with: THERMOMARK W, THERMOMARK ROLL, THERMOMARK X, Unperforated, Mounting type: Slide on, Cable diameter: 6.4-19.1 mm, Lettering field: 30 x 80000 mm

The figure shows the WMS 12,7 (Ex20)R version

## Product Features

- Available in the form of continuous rolls and can be printed on both sides using the THERMOMARK W2 printer
- The shrink sleeves are automatically perforated or cut to the required length during the printing process
- UL 224 (125°C, 600 V, VW-1)
- CSA.C22.2 No. 198.1 (125°C, 600 V, VW-1)
- MIL-STD-202G, SAE AMS-DTL-23053, SAE AS-81531
- Individual markers can be cut to any length up to 1 m

## Key commercial data

<b>package_quantity</b>	1
<b>GTIN</b>	4046356625951

## Technical data

### Dimensions

<b>Length (b)</b>	80 m
<b>Width (a)</b>	30 mm

### Ambient conditions

<b>Wipe resistance</b>	DIN EN 61010-1 (VDE 0411-1)
<b>Ambient temperature (operation)</b>	-55 °C ... 135 °C

### General

<b>Color</b>	white
<b>Base element material</b>	polyolefine
<b>Components</b>	Halogen-free
<b>Material</b>	Polyolefine

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	24190219
<b>eCl@ss 4.1</b>	24190219

# Shrink sleeve - WMS 19,1 (EX30)RL - 0800326

## classifications

### eCl@ss

eCl@ss 5.0	27400401
eCl@ss 5.1	27400401
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401

### ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC001530
ETIM 4.0	EC001530
ETIM 5.0	EC001530

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

## accessories

### Ink ribbon

THERMOMARK-RIBBON 64-WMSU - 0801360



THERMOMARK-RIBBON 110-WMSU - 0801358



## Printing system accessories

## Shrink sleeve - WMS 19,1 (EX30)RL - 0800326

accessories

THERMOMARK-ERH 500 - 5146309



---

### Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>