

Shrink sleeve - WMS 3,2 (EX5)R YE - 0800301

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Shrink tube for THERMOMARK W1 on a roll, 1 roll = 30 m

The figure shows the WMS 12,7 (E.20)R YE version

Product Features

- Available in the form of continuous rolls and can be printed on both sides using the THERMOMARK W2 printer
- The shrink sleeves are automatically perforated or cut to the required length during the printing process
- UL 224 (125°C, 600 V, VW-1)
- MIL-STD-202G, SAE AMS-DTL-23053, SAE AS-81531
- CSA.C22.2 No. 198.1 (125°C, 600 V, VW-1)
- Individual markers can be cut to any length up to 1 m

Key commercial data

package_quantity	1
GTIN	4046356625982

Technical data

Dimensions

Length (b)	30 m
Width (a)	5 mm

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-55 °C ... 135 °C

General

Color	yellow
Base element material	polyolefine
Components	Halogen-free
Material	Polyolefine
Number of individual labels	1000
Number of individual labels per row	1

classifications

eCl@ss

Shrink sleeve - WMS 3,2 (EX5)R YE - 0800301

classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27400401
eCl@ss 5.1	27400401
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC001530
ETIM 4.0	EC001530
ETIM 5.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

accessories

Ink ribbon

THERMOMARK-RIBBON 110-WMSU - 0801358



THERMOMARK-RIBBON 64-WMSU - 0801360



Shrink sleeve - WMS 3,2 (EX5)R YE - 0800301

accessories

THERMOMARK-RIBBON 64-WMSU WH - 0801361



THERMOMARK-RIBBON 110-WMSU WH - 0801359



Printing system accessories

THERMOMARK ROLL-ERH - 5146448



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>