

Surge protection connector - PT-IQ-2X2-24DC-P - 2800804

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Surge protection plug with integrated multi-stage status indicator on the module for two 2-wire floating signal circuits. 24 V DC nominal voltage.

Product Features

- ✓ Surge protection system
- ✓ Multi-level state monitoring
- ✓ Collective message about supply and remote module
- ✓ System supplied via DIN rail bus
- ✓ Up to 28 protection modules per supply module
- ✓ Maximum ease of maintenance thanks to the two-piece design
- ✓ Codable plug
- ✓ Impedance-neutral disconnection of plug for maintenance purposes
- ✓ Base element remains an integral part of the installation



Key commercial data

package_quantity	1
GTIN	4046356659185

Technical data

Dimensions

Width	17.7 mm
Depth	46.6 mm
Pitch unit	1 Div.
Height	91.1 mm
Width	17.7 mm
Depth	77.5 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Degree of protection	IP20

General

Housing material	PA 6.6
------------------	--------

Surge protection connector - PT-IQ-2X2-24DC-P - 2800804

Technical data

General

Inflammability class according to UL 94	V0
Color	black
Mounting type	On base element
Design	Male
Direction of action	Line-Line & Line-Signal Ground/Shield & optional Signal Ground/ Shield-Earth Ground

Protective circuit

Nominal voltage U_N	24 V DC
Maximum continuous operating voltage U_C	30 V DC
Maximum continuous operating voltage U_C	21 V AC
Nominal current I_N	700 mA (Up to 45°C)
Total surge current (8/20) μs	20 kA

classifications

eCl@ss

eCl@ss 4.0	27140201
eCl@ss 4.1	27130801
eCl@ss 5.0	27130801
eCl@ss 5.1	27130801
eCl@ss 6.0	27130807
eCl@ss 7.0	27130807
eCl@ss 8.0	27130807

ETIM

ETIM 3.0	EC000943
ETIM 4.0	EC000943
ETIM 5.0	EC000943

UNSPSC

UNSPSC 6.01	30212010
UNSPSC 7.0901	39121610
UNSPSC 11	39121610
UNSPSC 12.01	39121610
UNSPSC 13.2	39121620

accessories

Marker pen

Surge protection connector - PT-IQ-2X2-24DC-P - 2800804

accessories

X-PEN 0,35 - 0811228



Terminal marking

ZBF 5:UNBEDRUCKT - 0808642



ZBF 5/WH-100:UNBEDRUCKT - 0808668



Labeled terminal marker

ZBF 5,LGS:FORTL.ZAHLEN - 0808671



ZBF 5,LGS:GERADE ZAHLEN - 0810821



Surge protection connector - PT-IQ-2X2-24DC-P - 2800804

accessories

ZBF 5,LGS:UNGERADE ZAHLEN - 0810863



ZBF 5,QR:FORTL.ZAHLEN - 0808697



Device marking

ZBN 18:UNBEDRUCKT - 2809128



accessories

ZBF 15:SO/CMS - 0814717



ZBF 5:SO/CMS - 0808707



Surge protection connector - PT-IQ-2X2-24DC-P - 2800804


accessories

ZBN 18:SO/CMS - 0800763



Drawings

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>