



Data sheet | Item number: 756-5312/040-015

Sensor/actuator cable; fitted on one end (with free end); 4-pole; M12 plug, angled; one free cable end; 1.5 m



www.wago.com/756-5312/040-015





| Pin 1 ... 5: 0,34 mm ² | |
|-----------------------------------|-------------|
| 1 | braun (+) |
| 2 | weiß (Ö) |
| 3 | blau (-) |
| 4 | schwarz (S) |
| 5 | grau |
| Schirm | |

Item description

Short description:

- PUR, halogen-free
- Suitable for drag chains
- Good resistance to microbes, hydrolysis, oil, chemicals and UV radiation.
- Good chemical resistance.
- Cable used: UL listed

Data

Technical Data

| | |
|---|---------------------|
| Connection type | M12 plug - free end |
| No. of poles | 4 |
| Leitungsanschlussrichtung zur Steckrichtung | 90° |
| Steckgesichtskodierung Leitung/Adapter 1 1 | A coded |
| Cable length | 1.5 m |
| Operating voltage | AC/DC 250 V |
| Operating current | 4 A |
| Rated surge voltage | 2,5 kV |

Mechanical data

| | |
|-------------------------------|--|
| Bending cycles | 2 |
| Schleppkettentauglichkeit | yes |
| Color of sheathed cable | black |
| Durchmesser der Mantelleitung | 4.5 ... 4.9 mm |
| Sheath material | Polyurethane (OPUR), halogen-free per DIN VDE 0472 Part 815, flame resistant per IEC 332-2, self-extinguishing |
| Halogen-free | Yes |
| Housing material | Polyurethan (PUR) |
| Contact material | CuSn |
| Contact plating | CuNi/Au |
| Tightening torque | 1 Nm |
| Weight | 65 g |

Environmental Requirements

| | |
|--------------------------------------|--------------------|
| Umgebungstemperatur (Betrieb) bewegt | -25 ... +90 °C |
| Umgebungstemperatur (Betrieb) ruhend | -50 ... +90 °C |
| Degree of protection | IP67 |
| Degree of pollution (5) | 3 acc. to VDE 0110 |

Commercial data

| | |
|--------------------|---------------|
| Country of origin | HU |
| GTIN | 4045454942304 |
| Customs Tariff No. | 85444290900 |

Downloads

Documentation

System Description

| | | | |
|--------------------------------------|-------------|----------|--------------------------|
| IP67 Cables and Pluggable Connectors | Jun 6, 2017 | 434.4 kB | Download |
|--------------------------------------|-------------|----------|--------------------------|

Subject to changes.