


Data sheet | Item number: 756-5507/040-010

Sensor/actuator cable; fitted on both ends; 4-pole; M8 socket, straight; M12 plug, straight; 1 m




www.wago.com/756-5507/040-010



RoHS Compliant

BOMcheck.net



Pin 1 ... 4: 0,34 mm²

| | | |
|---|-------------|---|
| 1 | braun (+) | 1 |
| 2 | weiß (Ö) | 2 |
| 3 | blau (-) | 3 |
| 4 | schwarz (S) | 4 |

Item description

Short description:

- PUR, halogen-free
- Suitable for drag chains
- Good resistance to microbes, hydrolysis, oil, chemicals and UV radiation.
- Good chemical resistance.
- Cable used: UL listed



Data

Technical Data

| | |
|---|----------------------|
| Connection type | M8 socket - M12 plug |
| No. of poles | 4 |
| Leitungsanschlussrichtung zur Steckrichtung | 0° |
| Leitungsanschlussrichtung zur Steckrichtung (2) | 0° |
| Steckgesichtskodierung Leitung/Adapter 2 1 | A coded |
| Cable length | 1 m |
| Operating voltage | AC/DC 60 V |
| Operating current | 4 A |
| Rated surge voltage | 1,5 kV |

Mechanical data

| | |
|-------------------------------|--|
| Bending cycles | 2 |
| Schleppkettentauglichkeit | yes |
| Color of sheathed cable | black |
| Durchmesser der Mantelleitung | 3.9 ... 4.3 mm |
| Sheath material | Polyurethane (OPUR), halogen-free per DIN VDE 0472 Part 815, flame resistant per IEC 332-2, self-extinguishing |
| Halogen-free | Yes |
| Housing material | Polyurethan (PUR) |
| Contact material | CuSn |
| Contact plating | CuNi/Au |
| Tightening torque | 0.6 ... 1 Nm |
| Weight | 44 g |

Environmental Requirements

| | |
|--------------------------------------|--------------------|
| Umgebungstemperatur (Betrieb) bewegt | -25 ... +90 °C |
| Umgebungstemperatur (Betrieb) ruhend | -50 ... +90 °C |
| Degree of protection | IP67 |
| Degree of pollution (5) | 3 acc. to VDE 0110 |

Commercial data

| | |
|--------------------|---------------|
| Country of origin | DE |
| GTIN | 4044918975933 |
| Customs Tariff No. | 85444290900 |

Downloads

Documentation

System Description



Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.