

Printed-circuit board connector - PTS 1,5/ 2-PH-5,0 - 1805517

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Plug component, Nominal current: 10 A, Rated voltage (III/2): 400 V, Number of positions: 2, Pitch: 5 mm, Connection method: Spring-cage conn., Color: green

Key commercial data

package_quantity	250
GTIN	4046356679121

Technical data

Dimensions

Pitch	5 mm
Dimension a	5 mm

General

Range of articles	PTS 1,5/...-PH
Insulating material group	I
Rated surge voltage (III/3)	4 kV
Rated surge voltage (III/2)	4 kV
Rated surge voltage (II/2)	4 kV
Rated voltage (III/3)	250 V
Rated voltage (III/2)	400 V
Rated voltage (II/2)	600 V
Nominal current I _N	10 A
Nominal cross section	2.5 mm ²
Insulating material	PA
Inflammability class according to UL 94	V0
Stripping length	8 mm
Number of positions	2

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.25 mm ²

Printed-circuit board connector - PTS 1,5/ 2-PH-5,0 - 1805517

Technical data

Connection data

Conductor cross section stranded, with ferrule without plastic sleeve max.	1.5 mm²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.25 mm² 1
Conductor cross section stranded, with ferrule with plastic sleeve max.	1 mm²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	14

classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27141109
eCl@ss 5.0	27141190
eCl@ss 5.1	27141190
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002637

UNSPSC

UNSPSC 6.01	30211801
UNSPSC 7.0901	39121432
UNSPSC 11	34131203
UNSPSC 12.01	39121432
UNSPSC 13.2	39121432

approvals

GOST /


Approval details

GOST 
--

Drawings

Printed-circuit board connector - PTS 1,5/ 2-PH-5,0 - 1805517

Diagram



Type: PTS 1,5/...-PH-5,0 with PST 1,3/...-5,0

Dimensioned drawing

