

Y distributor - SAC-5P-M12Y/2XM12FS VP S21 - 1514029

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Y-distributor, 5-pos., straight M12 plug on 2 x straight M12 socket, parallel distributor, inner gauge of 21 mm

The illustration shows the green standard version

Key commercial data

package_quantity	5
GTIN	4017918943509

Technical data

Dimensions

Center distance	21 mm
-----------------	-------

Ambient conditions

Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
Degree of protection	IP65
Degree of protection	IP67

General

Rated current at 40°C	4 A
Rated voltage	60 V
Number of positions	5
Contact resistance	≤ 5 mΩ
Insulation resistance	≥ 100 MΩ
Coding	A - standard
Standards/regulations	M12 connector IEC 61076-2-101
Status display	No
Surge voltage category	II
Pollution degree	3
Insertion/withdrawal cycles	≥ 100
Torque	0.4 Nm (M12 connector)

Material

Inflammability class according to UL 94	HB
Contact material	CuZn
Contact surface material	Ni/Au

Y distributor - SAC-5P-M12Y/2XM12FS VP S21 - 1514029

Technical data

Material

Contact carrier material	TPU GF
Material of grip body	TPU, hardly inflammable, self-extinguishing
Material, knurls	Zinc die-cast, nickel-plated
Sealing material	NBR

Cable

classifications

eCl@ss

eCl@ss 4.0	27060306
eCl@ss 4.1	27060306
eCl@ss 5.0	27061801
eCl@ss 5.1	27061801
eCl@ss 6.0	27061801
eCl@ss 7.0	27061801
eCl@ss 8.0	27061801

ETIM

ETIM 2.0	EC000830
ETIM 3.0	EC001855
ETIM 4.0	EC001855
ETIM 5.0	EC001855


UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31251501

approvals

GOST /

Approval details



accessories

Torque tool

Y distributor - SAC-5P-M12Y/2XM12FS VP S21 - 1514029

accessories

TSD 04 SAC - 1208429



Screwdriver tools

SAC BIT M12-D15 - 1208432



Protective cap

PROT-M12 - 1680539




PROT-M12 FS - 1560251



Drawings

Y distributor - SAC-5P-M12Y/2XM12FS VP S21 - 1514029


Dimensioned drawing



Plug M12 x 1, Y distributor, inner gauge of 21 mm

Y distributor - SAC-5P-M12Y/2XM12FS VP S21 - 1514029


Circuit diagram



Contact assignment of the M12 Y distributor

Y distributor - SAC-5P-M12Y/2XM12FS VP S21 - 1514029


Schematic diagram



Pin assignment M12 male connector, 5-pos., A-coded, male side


Y distributor - SAC-5P-M12Y/2XM12FS VP S21 - 1514029

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

Schematic diagram



Layout of connector pin assignments

