

## Cable duct - CD 60X100 - 3240263

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Cable duct, gray, consisting of upper and lower part, width: 60 mm, height: 100 mm, length 2000 mm

### Product Features

- Easy, burr-free cutting with minimum effort using the CUTFOX-CD cable duct cutter
- Thanks to its leverage and special cutting geometry, the PPS CD cable duct cutter enables easy, burr-free cutting with minimum effort
- Predetermined breaking point enables tool-free, burr-free removal of bars
- The wide, diagonal heads of the cable duct bars make it easy to fit the cover and hold it securely in place
- Installed conductors are securely held in place by means of wire retaining clips that can be snapped onto bars on the side
- Plastic body-bound rivets enable easy fixing of cable ducts using the rivet setting tool

### Key commercial data

<b>package_quantity</b>	8
<b>GTIN</b>	4046356464727

### Technical data

#### Dimensions

<b>Length (b)</b>	2000 mm
<b>Height</b>	100 mm
<b>Width (a)</b>	60 mm

#### Ambient conditions

<b>Ambient temperature (operation)</b>	-5 °C ... 60 °C
--	-----------------

#### General

<b>Color</b>	gray
<b>Components</b>	Lead-free
<b>Inflammability class according to UL 94</b>	V0
<b>Material</b>	PVC

### classifications

#### eCl@ss

<b>eCl@ss 4.0</b>	27140602
<b>eCl@ss 4.1</b>	27140602

# Cable duct - CD 60X100 - 3240263

## classifications

### eCl@ss

eCl@ss 5.0	27140602
eCl@ss 5.1	27140602
eCl@ss 6.0	27400703
eCl@ss 7.0	27400703
eCl@ss 8.0	27400703

### ETIM

ETIM 2.0	EC000012
ETIM 3.0	EC000012
ETIM 4.0	EC000012
ETIM 5.0	EC000012



### UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708

## approvals

CSA / UL Recognized / VDE Zeichengenehmigung /

### Approval details



## accessories

### Cover

## Cable duct - CD 60X100 - 3240263

### accessories

CD COVER 60 - 3240287



---

### Filler plug

RVT-PA 4 - 3240498



RVT-PA 6 - 3240499



---

### Riveting tools

UNIFOX-RVT P 4 - 1212478



UNIFOX-RVT P 6 - 1212509



---

### Slotted cable trunking system

# Cable duct - CD 60X100 - 3240263


accessories

CD WR - 3240284



## Drawings

Dimensioned drawing



Base perforation according to DIN EN 50085

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>