

## Shrink sleeve - WMS 3,2 (EX5)R - 0800290

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Shrink sleeve, Roll, white, Unlabeled, Can be labeled with: THERMOMARK W, THERMOMARK ROLL, THERMOMARK X, Unperforated, Mounting type: Slide on, Cable diameter: 1-3.2 mm, Lettering field: 5 x 30000 mm

The figure shows the WMS 12,7 (Ex20)R version

### Product Features

- ✓ Available in the form of continuous rolls and can be printed on both sides using the THERMOMARK W2 printer
- ✓ The shrink sleeves are automatically perforated or cut to the required length during the printing process
- ✓ UL 224 (125°C, 600 V, VW-1)
- ✓ MIL-STD-202G, SAE AMS-DTL-23053, SAE AS-81531
- ✓ CSA.C22.2 No. 198.1 (125°C, 600 V, VW-1)
- ✓ Individual markers can be cut to any length up to 1 m

### Key commercial data

|                  |               |
|------------------|---------------|
| package_quantity | 1             |
| GTIN             | 4046356625791 |

### Technical data

#### Dimensions

|            |      |
|------------|------|
| Length (b) | 30 m |
| Width (a)  | 5 mm |

#### Ambient conditions

|                                 |                             |
|---------------------------------|-----------------------------|
| Wipe resistance                 | DIN EN 61010-1 (VDE 0411-1) |
| Ambient temperature (operation) | -55 °C ... 135 °C           |

#### General

|                                     |              |
|-------------------------------------|--------------|
| Color                               | white        |
| Base element material               | polyolefine  |
| Components                          | Halogen-free |
| Material                            | Polyolefine  |
| Number of individual labels         | 1000         |
| Number of individual labels per row | 1            |

### classifications

eCl@ss

## Shrink sleeve - WMS 3,2 (EX5)R - 0800290

### classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 24190219 |
| eCl@ss 4.1 | 24190219 |
| eCl@ss 5.0 | 27400401 |
| eCl@ss 5.1 | 27400401 |
| eCl@ss 6.0 | 27400401 |
| eCl@ss 7.0 | 27400401 |
| eCl@ss 8.0 | 27400401 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC001530 |
| ETIM 4.0 | EC001530 |
| ETIM 5.0 | EC001530 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39121410 |

### accessories

#### Ink ribbon

THERMOMARK-RIBBON 64-WMSU - 0801360



THERMOMARK-RIBBON 110-WMSU - 0801358



### Printing system accessories

# Shrink sleeve - WMS 3,2 (EX5)R - 0800290

accessories

THERMOMARK ROLL-ERH - 5146448



---

## Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>