

# Marker strip - SK 2,8 WH:REEL - 0805205

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Marker strip, Roll, white, Unlabeled, Can be labeled with: THERMOMARK ROLL, THERMOMARK X, THERMOMARK S1.1, Mounting type: Adhesive

## Product Features

- The markers supplied in card format can be easily labeled using standard laser printers
- The markers that are supplied in roll format can be labeled quickly and cost-effectively using THERMOMARK printers
- The SK labeling range offers self-adhesive marker strips for labeling products that do not have a marker groove
- Ideal for labeling COMBICON connectors
- Labeling service: Phoenix Contact can custom-label SK markers according to your requirements
- The SK labeling range offers self-adhesive marker strips for labeling products that do not have a marker groove

## Key commercial data

<b>package_quantity</b>	1
<b>GTIN</b>	4017918245139

## Technical data

### Dimensions

<b>Length (b)</b>	90 m
<b>Width (a)</b>	2.8 mm
<b>Inner diameter (f)</b>	76.00 mm

### Ambient conditions

<b>Wipe resistance</b>	DIN EN 61010-1 (VDE 0411-1)
<b>Ambient temperature (operation)</b>	-40 °C ... 150 °C

### General

<b>Color</b>	white
<b>Base element material</b>	Polyester
<b>Components</b>	free from silicone and halogen
<b>Inflammability class according to UL 94</b>	V2
<b>Material</b>	Polyester
<b>Number of individual labels</b>	480000
<b>Number of individual labels per row</b>	10
<b>Number of marker strips</b>	14

# Marker strip - SK 2,8 WH:REEL - 0805205

## classifications

### eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

### ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

## accessories

### Marker pen

B-STIFT - 1051993



---

### Ink ribbon

THERMOMARK-RIBBON 110 - 5145384



---

## Drawings

