

# Short-circuit connector - CTM EST - 2838649

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



LSA-PLUS grounding plug (COMTRAB CTM) to short-circuit and ground potentials in CT-TERMIBLOCK... and disconnect strip CT 10...

## Product Features

- Grounding plug to short circuit and ground the wires

## Key commercial data

package_quantity	10
GTIN	4017918907631

## Technical data

### Dimensions

Height	21 mm
Width	9.5 mm
Depth	53.5 mm

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 75 °C
Degree of protection	IP20

### General

Housing material	PA
Inflammability class according to UL 94	V0
Color	black
Standards for air and creepage distances	DIN VDE 0110-1
Standards for air and creepage distances	IEC 60664-1
Mounting type	On CT-TERMIBLOCK and LSA-PLUS disconnect strip
Design	LSA-PLUS module
Number of positions	2

### Protective circuit

Nominal current I <sub>N</sub>	1.5 A (25 °C)
Total surge current (8/20) μs	10 kA
Total surge current (10/350) μs	2.5 kA
Message: Surge protection fault	None

### Connection data

# Short-circuit connector - CTM EST - 2838649

## Technical data

### Connection data

<b>Connection type IN</b>	COMTRAB plug-in system
<b>Connection type OUT</b>	COMTRAB plug-in system
<b>Connection method</b>	LSA-PLUS

### Connection, equipotential bonding

<b>Connection method</b>	Spring contact
--------------------------	----------------

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	27060306
<b>eCl@ss 4.1</b>	27060306
<b>eCl@ss 5.0</b>	27061801
<b>eCl@ss 5.1</b>	27141190
<b>eCl@ss 6.0</b>	27141190
<b>eCl@ss 7.0</b>	27141190
<b>eCl@ss 8.0</b>	27141190

### ETIM

<b>ETIM 2.0</b>	EC000490
<b>ETIM 3.0</b>	EC000490
<b>ETIM 4.0</b>	EC000448
<b>ETIM 5.0</b>	EC002848

### UNSPSC

<b>UNSPSC 6.01</b>	31251501
<b>UNSPSC 7.0901</b>	31251501
<b>UNSPSC 11</b>	31251501
<b>UNSPSC 12.01</b>	31251501
<b>UNSPSC 13.2</b>	31251501

## approvals

GOST /


### Approval details


---

## Drawings

# Short-circuit connector - CTM EST - 2838649

Dimensioned drawing



Circuit diagram

