

Flush-type connector - SACC-DSIV-M 8FS-3CON-L180-06 - 1524776

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sensor/actuator flush-type socket, 3-pos., M8, rear/screw mounting with M8 thread, polarity protection, with straight solder connection, model with 6 mm long terminal pins

Key commercial data

package_quantity	20
GTIN	4017918950101

Technical data

Ambient conditions

Ambient temperature (operation)	-25 °C ... 85 °C
Degree of protection	IP67

General

Rated current at 40°C	4 A
Rated voltage	60 V
Number of positions	3
Contact resistance	≤ 3 mΩ
Insulation resistance	≥ 100 MΩ
Coding	A - standard
Standards/regulations	M8 connector IEC 61076-2-104
Status display	No
Surge voltage category	II
Pollution degree	3
Connection method	Solder pins
Mounting type	Rear mounting M8 x 1 With locking nut

Material

Inflammability class according to UL 94	HB
Contact material	CuSn
Contact surface material	Au
Contact carrier material	PA 66
Material, knurls	Nickel-plated brass
Sealing material	NBR

Flush-type connector - SACC-DSIV-M 8FS-3CON- L180-06 - 1524776

classifications

eCl@ss

eCl@ss 4.0	27140815
eCl@ss 4.1	27140815
eCl@ss 5.0	27143423
eCl@ss 5.1	27143423
eCl@ss 6.0	27143423
eCl@ss 7.0	27449001
eCl@ss 8.0	27449001

ETIM

ETIM 2.0	EC001297
ETIM 3.0	EC002061
ETIM 4.0	EC002062
ETIM 5.0	EC002062

UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31251501

approvals

GOST /


Approval details

 GOST
--

Drawings

Flush-type connector - SACC-DSIV-M 8FS-3CON- L180-06 - 1524776


Drilling diagram



Drilling diagram

Flush-type connector - SACC-DSIV-M 8FS-3CON-L180-06 - 1524776


Dimensioned drawing



M8 flush-type socket

Flush-type connector - SACC-DSIV-M 8FS-3CON- L180-06 - 1524776


Dimensioned drawing



Mounting panel with feed-through hole

Flush-type connector - SACC-DSIV-M 8FS-3CON- L180-06 - 1524776

Schematic diagram



Pin assignment M8 socket, 3-pos., view female side

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>