

## Marker pin Zack strip - BN-ZB 7,5/WH:UNBEDRUCKT - 1401844

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Marker pin Zack strip, Strip, white, Unlabeled, Can be labeled with: Plotter, Mounting type: Plug in, For terminal block width: 7.5 mm, Lettering field: 6 x 4 mm

The illustration shows version  
BN-ZB 7,5 -UNPRINTED, -  
CONSEC. NOS and BNB-ZB 7,5  
SO/CMS

### Key commercial data

|                  |               |
|------------------|---------------|
| package_quantity | 10            |
| GTIN             | 4017918020583 |

### Technical data

#### Dimensions

|           |      |
|-----------|------|
| Width (a) | 6 mm |
|-----------|------|

#### Ambient conditions

|                                 |                             |
|---------------------------------|-----------------------------|
| Wipe resistance                 | DIN EN 61010-1 (VDE 0411-1) |
| Ambient temperature (operation) | -40 °C ... 100 °C           |

#### General

|                                         |                                |
|-----------------------------------------|--------------------------------|
| Note                                    | Can be labeled with CMS        |
| Color                                   | white                          |
| Components                              | free from silicone and halogen |
| Inflammability class according to UL 94 | V2                             |
| Material                                | PA                             |
| Number of individual labels             | 10                             |
| Number of individual labels per row     | 10                             |
| Number of marker strips                 | 10                             |

### classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 24190208 |
| eCl@ss 4.1 | 24190208 |
| eCl@ss 5.0 | 27149103 |
| eCl@ss 5.1 | 27141137 |

## Marker pin Zack strip - BN-ZB 7,5/WH:UNBEDRUCKT - 1401844

### classifications

#### eCl@ss

|                   |          |
|-------------------|----------|
| <b>eCl@ss 6.0</b> | 27141137 |
| <b>eCl@ss 7.0</b> | 27141137 |
| <b>eCl@ss 8.0</b> | 27141137 |

#### ETIM

|                 |          |
|-----------------|----------|
| <b>ETIM 2.0</b> | EC000761 |
| <b>ETIM 3.0</b> | EC000761 |
| <b>ETIM 4.0</b> | EC000761 |
| <b>ETIM 5.0</b> | EC000761 |

#### UNSPSC

|                      |          |
|----------------------|----------|
| <b>UNSPSC 6.01</b>   | 30211811 |
| <b>UNSPSC 7.0901</b> | 39121410 |
| <b>UNSPSC 11</b>     | 39121410 |
| <b>UNSPSC 12.01</b>  | 39121410 |
| <b>UNSPSC 13.2</b>   | 39121410 |

### Drawings