

## End cover - D-PT 1,5/S - 3208142

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



End cover, Length: 45 mm, Width: 2.2 mm, Height: 24.3 mm, Color: gray

### Key commercial data

|                         |               |
|-------------------------|---------------|
| <b>package_quantity</b> | 50            |
| <b>GTIN</b>             | 4046356564397 |

### Technical data

#### General

|                                                |      |
|------------------------------------------------|------|
| <b>Color</b>                                   | gray |
| <b>Insulating material</b>                     | PA   |
| <b>Inflammability class according to UL 94</b> | V0   |

#### General

|                                                                              |        |
|------------------------------------------------------------------------------|--------|
| <b>Temperature index, insulating material (DIN EN 60216-1 (VDE 0304-21))</b> | 130 °C |
| <b>Static insulating material application in cold</b>                        | -60 °C |

#### Dimensions

|               |         |
|---------------|---------|
| <b>Width</b>  | 2.2 mm  |
| <b>Length</b> | 45 mm   |
| <b>Height</b> | 24.3 mm |

### classifications

#### eCl@ss

|                   |          |
|-------------------|----------|
| <b>eCl@ss 4.0</b> | 27141199 |
| <b>eCl@ss 4.1</b> | 27141199 |
| <b>eCl@ss 5.0</b> | 27141145 |
| <b>eCl@ss 5.1</b> | 27141145 |
| <b>eCl@ss 6.0</b> | 27141133 |
| <b>eCl@ss 7.0</b> | 27141133 |
| <b>eCl@ss 8.0</b> | 27141133 |

#### ETIM

|                 |          |
|-----------------|----------|
| <b>ETIM 4.0</b> | EC000886 |
|-----------------|----------|

## End cover - D-PT 1,5/S - 3208142

### classifications

#### ETIM

|                 |          |
|-----------------|----------|
| <b>ETIM 5.0</b> | EC000886 |
|-----------------|----------|

#### UNSPSC

|                      |          |
|----------------------|----------|
| <b>UNSPSC 6.01</b>   | 30211827 |
| <b>UNSPSC 7.0901</b> | 39121424 |
| <b>UNSPSC 11</b>     | 39121424 |
| <b>UNSPSC 12.01</b>  | 39121424 |
| <b>UNSPSC 13.2</b>   | 39121424 |

### approvals

---

GOST /

---

#### Approval details



### Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>