

## Cable duct - CD-HF 30X80 - 3240346

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Cable duct, light gray, halogen-free, consisting of upper part and mounting base, width: 30 mm, height: 80 mm, length: 2000 mm

The illustration shows the version in gray

### Product Features

- Predetermined breaking point enables tool-free, burr-free removal of bars
- Fast and seamless creation of T and cross connections by means of an additional predetermined breaking point in the cable duct base
- The wide, diagonal heads of the cable duct bars make it easy to fit the cover and hold it securely in place
- Installed conductors are securely held in place by means of wire retaining clips that can be snapped onto bars on the side
- Cover is securely held in place for both horizontal and vertical mounting

### Key commercial data

<b>package_quantity</b>	12
<b>GTIN</b>	4046356508315

### Technical data

#### Dimensions

<b>Length (b)</b>	2000 mm
<b>Height</b>	80 mm
<b>Width (a)</b>	30 mm

#### Ambient conditions

<b>Ambient temperature (operation)</b>	-25 °C ... 90 °C
--	------------------

#### General

<b>Color</b>	light gray
<b>Components</b>	Halogen-free
<b>Inflammability class according to UL 94</b>	V0
<b>Material</b>	PC/ABS

### classifications

#### eCl@ss

<b>eCl@ss 4.0</b>	27140602
<b>eCl@ss 4.1</b>	27140602

# Cable duct - CD-HF 30X80 - 3240346

## classifications

### eCl@ss

eCl@ss 5.0	27140602
eCl@ss 5.1	27140602
eCl@ss 6.0	27400703
eCl@ss 7.0	27400703
eCl@ss 8.0	27400703

### ETIM

ETIM 2.0	EC000012
ETIM 3.0	EC000012
ETIM 4.0	EC000012
ETIM 5.0	EC000012



### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121411
UNSPSC 11	39121411
UNSPSC 12.01	39121708
UNSPSC 13.2	39121411

## approvals

CSA / UL Recognized / VDE Zeichengenehmigung /

### Approval details



## accessories

### Cover

## Cable duct - CD-HF 30X80 - 3240346

### accessories

CD-HF COVER 30 - 3240370



---

### Filler plug

RVT-PA 4 - 3240498



RVT-PA 6 - 3240499



---

### Riveting tools

UNIFOX-RVT P 4 - 1212478



UNIFOX-RVT P 6 - 1212509




---

### Drawings

## Cable duct - CD-HF 30X80 - 3240346

Dimensioned drawing



Base perforation according to DIN EN 50085

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>