

## Plastic label - UC-EMLP (11X9) - 0819291

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Plastic label, Sheet, white, Unlabeled, Can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Adhesive, Lettering field: 11 x 9 mm

### Product Features

- ✓ The UC-EMLP ... UniCard labeling range includes self-adhesive device markers with good adhesive properties
- ✓ The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the BLUEMARK LED
- ✓ Self-adhesive with good adhesive properties
- ✓ The wide temperature range means that the labels can be used in control cabinets as well as the field
- ✓ The sheets provide space for including function texts
- ✓ The format automatically ensures printing with a high degree of positioning accuracy

### Key commercial data

|                  |               |
|------------------|---------------|
| package_quantity | 10            |
| GTIN             | 4046356152433 |

### Technical data

#### Dimensions

|            |       |
|------------|-------|
| Length (b) | 11 mm |
| Width (a)  | 9 mm  |

#### Ambient conditions

|                                 |                             |
|---------------------------------|-----------------------------|
| Wipe resistance                 | DIN EN 61010-1 (VDE 0411-1) |
| Ambient temperature (operation) | -40 °C ... 120 °C           |

#### General

|                                          |                                |
|------------------------------------------|--------------------------------|
| Color                                    | white                          |
| Components                               | free from silicone and halogen |
| Inflammability class according to UL 94  | V2                             |
| Material                                 | PA                             |
| Number of individual labels              | 10                             |
| Number of individual labels per row      | 2                              |
| RoHS compliant                           | Yes                            |
| Adhesive                                 | Acrylic                        |
| Printability                             | InkJet, CMS                    |
| Test specification weathering-resistance | Following ISO 4892-2:2013-03   |
| Test duration                            | 96 h                           |

# Plastic label - UC-EMLP (11X9) - 0819291

## Technical data

### General

|                                                              |                         |
|--------------------------------------------------------------|-------------------------|
| Wipe resistance test result                                  | Test passed             |
| Salt spray test specification                                | DIN EN ISO 9227:2012-09 |
| Test duration                                                | 96 h                    |
| Salt spray testing result                                    | Test passed             |
| Alternating condensation climate with SO2 test specification | DIN 50018:1997-06       |
| Climate level                                                | KFW 1.0 S               |
| Cycles                                                       | 2                       |
| Condensation test result                                     | Test passed             |
| Burning behaviour                                            | self-extinguishing      |
| Adhesive strength                                            | 250 µm                  |

## classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 24190218 |
| eCl@ss 4.1 | 24190218 |
| eCl@ss 5.0 | 27141137 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |
| eCl@ss 8.0 | 27141137 |

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39121410 |

## accessories

### Magazine

# Plastic label - UC-EMLP (11X9) - 0819291

accessories

P1 UC-MAG 6 - 5146121



---

## Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>