

Cable duct - CD 60X60 - 3240193

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Wiring channel, gray, consisting of upper and lower part, width: 60 mm, height: 60 mm, length 2000 mm

Product Features

- ✓ Thanks to its leverage and special cutting geometry, the PPS CD cable duct cutter enables easy, burr-free cutting with minimum effort
- ✓ Easy, burr-free cutting with minimum effort using the CUTFOX-CD cable duct cutter
- ✓ Predetermined breaking point enables tool-free, burr-free removal of bars
- ✓ The wide, diagonal heads of the cable duct bars make it easy to fit the cover and hold it securely in place
- ✓ Installed conductors are securely held in place by means of wire retaining clips that can be snapped onto bars on the side
- ✓ Plastic body-bound rivets enable easy fixing of cable ducts using the rivet setting tool

Key commercial data

package_quantity	12
GTIN	4046356459181

Technical data

Dimensions

Length (b)	2000 mm
Height	60 mm
Width (a)	60 mm

Ambient conditions

Ambient temperature (operation)	-5 °C ... 60 °C
---------------------------------	-----------------

General

Color	gray
Components	Lead-free
Inflammability class according to UL 94	V0
Material	PVC

classifications

eCl@ss

eCl@ss 4.0	27140602
eCl@ss 4.1	27140602

Cable duct - CD 60X60 - 3240193

classifications

eCl@ss

eCl@ss 5.0	27140602
eCl@ss 5.1	27140602
eCl@ss 6.0	27400703
eCl@ss 7.0	27400703
eCl@ss 8.0	27400703

ETIM

ETIM 2.0	EC000012
ETIM 3.0	EC000012
ETIM 4.0	EC000012
ETIM 5.0	EC000012



UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708

approvals

CSA / UL Recognized / VDE Zeichengenehmigung /

Approval details



accessories

Cover

Cable duct - CD 60X60 - 3240193

accessories

CD COVER 60 - 3240287



Filler plug

RVT-PA 4 - 3240498



RVT-PA 6 - 3240499



Riveting tools

UNIFOX-RVT P 4 - 1212478



UNIFOX-RVT P 6 - 1212509



Slotted cable trunking system

Cable duct - CD 60X60 - 3240193


accessories

CD WR - 3240284



Drawings

Dimensioned drawing



Base perforation according to DIN EN 50085

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>