

Connector - C-SCFFI 1,5/4,8X0,8 - 3240537

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Slip-on sleeve, fully isolated, red, 0.5 - 1.5 mm², for plug 4.8 x 0.8 mm

Product Features

- Hard-soldered crimping zone for maximum conductor pull-out forces in connection with CRIMPFOX RCI... pliers
- Easy and reliable conductor entry thanks to 'EASY ENTRY'
- Halogen-free
- Electrolytically tin-plated

Key commercial data

| | |
|------------------|---------------|
| package_quantity | 50 |
| GTIN | 4046356528078 |

Technical data

Dimensions

| | |
|--|---------|
| Length (b) | 19.5 mm |
| Width (a) | 4.8 mm |
| Length of insulation sleeve (c) | 10.5 mm |
| Inner dimension of the insulating collar (d) | 4.3 mm |
| Material thickness (g) | 0.4 mm |

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -20 °C ... 105 °C |
| Short-term temperature | 120 °C |
| Max. permanent temperature | 105 °C |

General

| | |
|------------------|--------------|
| Color | red |
| Stripping length | 7 mm |
| Components | Halogen-free |
| Material | Brass |

classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27140815 |
|------------|----------|

Connector - C-SCFFI 1,5/4,8X0,8 - 3240537

classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.1 | 27140815 |
| eCl@ss 5.0 | 27260701 |
| eCl@ss 5.1 | 27260701 |
| eCl@ss 6.0 | 27400209 |
| eCl@ss 7.0 | 27440304 |
| eCl@ss 8.0 | 27440304 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000516 |
| ETIM 3.0 | EC000516 |
| ETIM 4.0 | EC000516 |
| ETIM 5.0 | EC000516 |


UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211923 |
| UNSPSC 7.0901 | 39121522 |
| UNSPSC 11 | 39121522 |
| UNSPSC 12.01 | 39121522 |
| UNSPSC 13.2 | 39121522 |

Drawings

Connector - C-SCFFI 1,5/4,8X0,8 - 3240537

Dimensioned drawing



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>