

## Cable lug - C-BCI 1,5/2,8 - 3240015

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Flat pin cable lug, red, 0.5 - 1.5 mm<sup>2</sup>,

### Product Features

- 'EASY ENTRY' for easy and reliable conductor entry
- Halogen-free
- Electrolytic tin plating

### Key commercial data

<b>package_quantity</b>	100
<b>GTIN</b>	4046356452632

### Technical data

#### Dimensions

<b>Length (b)</b>	28 mm
<b>Width (a)</b>	2.8 mm
<b>Length contact range</b>	17.5 mm
<b>Length of insulation sleeve (c)</b>	10.5 mm
<b>Inner dimension of the insulating collar (d)</b>	4 mm
<b>Material thickness (g)</b>	0.8 mm

#### Ambient conditions

<b>Ambient temperature (operation)</b>	-20 °C ... 105 °C
<b>Short-term temperature</b>	120 °C
<b>Max. permanent temperature</b>	105 °C

#### General

<b>Color</b>	red
<b>Stripping length</b>	7 mm
<b>Components</b>	Halogen-free
<b>Inflammability class according to UL 94</b>	V2
<b>Material</b>	Copper

### classifications

eCl@ss

## Cable lug - C-BCI 1,5/2,8 - 3240015

### classifications

#### eCl@ss

<b>eCl@ss 4.0</b>	27060701
<b>eCl@ss 4.1</b>	27060701
<b>eCl@ss 5.0</b>	27400201
<b>eCl@ss 5.1</b>	27400201
<b>eCl@ss 6.0</b>	27400201
<b>eCl@ss 7.0</b>	27400201
<b>eCl@ss 8.0</b>	27400201

#### ETIM

<b>ETIM 2.0</b>	EC000005
<b>ETIM 3.0</b>	EC000005
<b>ETIM 4.0</b>	EC001052
<b>ETIM 5.0</b>	EC001052


#### UNSPSC

<b>UNSPSC 6.01</b>	30212109
<b>UNSPSC 7.0901</b>	27121703
<b>UNSPSC 11</b>	27121703
<b>UNSPSC 12.01</b>	27121703
<b>UNSPSC 13.2</b>	27121703

### Drawings

## Cable lug - C-BCI 1,5/2,8 - 3240015

Dimensioned drawing



© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>