

Insert label - EMT (35X46)R - 0801604

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Insert label, Roll, white, Unlabeled, Can be labeled with: THERMOMARK ROLL, THERMOMARK X, THERMOMARK S1.1, Mounting type: Snapped into marker carrier, Lettering field: 35 x 46 mm

Product Features

- ✓ Can be printed using all the thermal transfer printers available from Phoenix Contact
- ✓ Insertable conductor marking for marking collars
- ✓ Thanks to their special shape, insert labels remain securely inside the collar once inserted
- ✓ Insert labels for marking various marking collars

Key commercial data

package_quantity	1
GTIN	4046356673099

Technical data

Dimensions

Length (b)	35 mm
Width (a)	46 mm

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C / 50 % relative humidity

General

Color	white
Components	free from silicone and halogen
Material	Polyester
Number of individual labels	500
Number of individual labels per row	2
RoHS compliant	Yes
Printability	Thermal transfer
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h

Insert label - EMT (35X46)R - 0801604

Technical data

General

Wipe resistance test result	Test passed
Salt spray test specification	DIN EN ISO 9227:2012-09
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:1997-06
Climate level	KFW 1.0 S
Cycles	2
Condensation test result	Test passed
Foil strength	175 µm

classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

accessories

Ink ribbon

THERMOMARK-RIBBON 110 - 5145384



Insert label - EMT (35X46)R - 0801604

accessories

Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>