

Label, highly flexible - EMLF (108XE)R YE - 0800550

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Label, highly flexible, Roll, yellow, Unlabeled, Can be labeled with: THERMOMARK ROLL, THERMOMARK X, THERMOMARK S1.1, Mounting type: Adhesive, Lettering field: 110 x 40000 mm

The figure shows the white version

Product Features

- ✓ Highly flexible, soft PVC label that adapts well to uneven surfaces
- ✓ Extremely high-quality appearance
- ✓ Outdoor-durable for up to eight years when subject to a temperature range of -50°C to +110°C
- ✓ Labeling service: Phoenix Contact can custom-label all EMLF ... markers according to your requirements

Key commercial data

package_quantity	1
GTIN	4046356606707

Technical data

Dimensions

Length (b)	40000 mm
Width (a)	108 mm

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 90 °C
Ambient temperature (assembly)	> 8 °C
Recommended storage conditions	23 °C / 50 % relative humidity

General

Color	yellow
Components	Silicone-free
Material	PVC
Number of individual labels	1
Number of individual labels per row	1
Adhesive	Acrylic
Printability	Thermal transfer
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h

Label, highly flexible - EMLF (108XE)R YE - 0800550

Technical data

General

Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	Following DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed
Foil strength	50 µm

classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

accessories

Ink ribbon

Label, highly flexible - EMLF (108XE)R YE - 0800550

accessories

THERMOMARK-RIBBON 110 - 5145384



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>