

Plastic label - US-EMLP (20X9) - 0828795

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Plastic label, Card, white, Unlabeled, Can be labeled with: THERMOMARK CARD PLUS, THERMOMARK CARD, Mounting type: Adhesive, Lettering field: 20 x 9 mm

Product Features

- The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and cost-effectively using the THERMOMARK CARD
- The US-EMLP ... UniSheet labeling range includes self-adhesive device markers with good adhesive properties
- The perforated markers are easy to separate and can be easily fitted
- The sheets provide space for including function texts

Key commercial data

| | |
|-------------------------|---------------|
| package_quantity | 10 |
| GTIN | 4046356558839 |

Technical data

Dimensions

| | |
|-------------------|--------|
| Length (b) | 20 mm |
| Height | 0.5 mm |
| Width (a) | 9 mm |

Ambient conditions

| | |
|--|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Ambient temperature (operation) | -30 °C ... 80 °C |

General

| | |
|--|---------------|
| Color | white |
| Components | Silicone-free |
| Inflammability class according to UL 94 | V0 |
| Material | PVC |
| Number of individual labels | 75 |
| Number of individual labels per row | 5 |

classifications

eCl@ss

| | |
|-------------------|----------|
| eCl@ss 4.0 | 24190219 |
|-------------------|----------|

Plastic label - US-EMLP (20X9) - 0828795

classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.1 | 24190219 |
| eCl@ss 5.0 | 27141137 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |
| eCl@ss 8.0 | 27141137 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39121410 |

accessories

Magazine

THERMOMARK CARD-US-MAG1 - 5146451



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>