

Cable duct - CD-HF 80X80 - 3240359

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Cable duct, light gray, halogen-free, consisting of upper part and mounting base, width: 80 mm, height: 80 mm, length: 2000 mm

The illustration shows the version in gray

Product Features

- ✓ Predetermined breaking point enables tool-free, burr-free removal of bars
- ✓ The wide, diagonal heads of the cable duct bars make it easy to fit the cover and hold it securely in place
- ✓ Fast and seamless creation of T and cross connections by means of an additional predetermined breaking point in the cable duct base
- ✓ Installed conductors are securely held in place by means of wire retaining clips that can be snapped onto bars on the side
- ✓ Cover is securely held in place for both horizontal and vertical mounting

Key commercial data

package_quantity	6
GTIN	4046356508445

Technical data

Dimensions

Length (b)	2000 mm
Height	80 mm
Width (a)	80 mm

Ambient conditions

Ambient temperature (operation)	-25 °C ... 90 °C
---------------------------------	------------------

General

Color	light gray
Components	Halogen-free
Inflammability class according to UL 94	V0
Material	PC/ABS

classifications

eCl@ss

eCl@ss 4.0	27140602
eCl@ss 4.1	27140602

Cable duct - CD-HF 80X80 - 3240359

classifications

eCl@ss

eCl@ss 5.0	27140602
eCl@ss 5.1	27140602
eCl@ss 6.0	27400703
eCl@ss 7.0	27400703
eCl@ss 8.0	27400703

ETIM

ETIM 2.0	EC000012
ETIM 3.0	EC000012
ETIM 4.0	EC000012
ETIM 5.0	EC000012



UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121411
UNSPSC 11	39121411
UNSPSC 12.01	39121708
UNSPSC 13.2	39121411

approvals

CSA / UL Recognized / VDE Zeichengenehmigung /

Approval details



accessories

Cover

Cable duct - CD-HF 80X80 - 3240359

accessories

CD-HF COVER 80 - 3240373



Slotted cable trunking system

CD WR - 3240284



Filler plug

RVT-PA 4 - 3240498



RVT-PA 6 - 3240499



Riveting tools

UNIFOX-RVT P 4 - 1212478



Cable duct - CD-HF 80X80 - 3240359


accessories

UNIFOX-RVT P 6 - 1212509



Drawings

Dimensioned drawing



Base perforation according to DIN EN 50085

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>