

Crimp contact - CK2,5-ED-3,00BU AG - 1663695

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Turned 2.5 crimp contact, individual female contact, core diameter 3.00 mm², silver-plated

Key commercial data

package_quantity	100
GTIN	4017918123505

Technical data

Electrical characteristics

Note	for HC-M-06, HC-M-HV, HC-M-08, HC-M-20, HC-A, HC-BB, HC-B and HC-HV contact carriers, the quality of a crimp connection is determined by the DIN EN 60 352-2
Contact resistance	≤ 0.003 Ω

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
--	-------------------

Mechanical characteristics

Conductor cross section	3 mm ²
Connection cross section AWG	13
Stripping length of the individual wire	7.5 mm (9.5 mm at HC-M-HV...)
Insertion/withdrawal cycles	≥ 500

General

Type	Individual female contact
Series	HC-M-06
Connection method	Crimp connection
Connection	for HC-M-06, HC-M-HV, HC-M-08, HC-M-20, HC-A, HC-BB, HC-B and HC-HV contact carriers. The quality of a crimp connection is determined by the DIN EN 60 352-2.

Material data

Contact material	Copper alloy
Contact surface material	hard-silver plated

classifications

eCl@ss

Crimp contact - CK2,5-ED-3,00BU AG - 1663695

classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

ETIM

ETIM 2.0	EC000796
ETIM 3.0	EC000796
ETIM 4.0	EC000796
ETIM 5.0	EC000796

UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	39121522
UNSPSC 11	39121522
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522

approvals

UL Recognized / GOST /

Approval details



accessories

Assembly tool

Crimp contact - CK2,5-ED-3,00BU AG - 1663695

accessories

CK1,6/2,5-MWZ - 1676734



CK2,5-EWZ - 1662722



Crimping tool

CRIMPFOX-1,6/2,5-ED-4,0 - 1687419



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>