

Insert label - EMT (103X23)R - 0800040

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Snap-in marker, for labeling Siemens controllers

Product Features

- ✓ Can be printed using all the thermal transfer printers available from Phoenix Contact
- ✓ Insertable conductor marking for marking collars
- ✓ Thanks to their special shape, insert labels remain securely inside the collar once inserted
- ✓ Insert labels for marking various marking collars
- ✓ Can be printed using all the thermal transfer printers available from Phoenix Contact
- ✓ Precise printing quality
- ✓ EMT ... insert strips are available in various sizes for marking controllers and modules from other manufacturers

Key commercial data

package_quantity	1
GTIN	4046356545402

Technical data

Dimensions

Length (b)	103 mm
Width (a)	23 mm

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C / 50 % relative humidity

General

Color	white
Components	free from silicone and halogen
Material	Polyester
Number of individual labels	500
Number of individual labels per row	1
RoHS compliant	Yes
Printability	Thermal transfer
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02

Insert label - EMT (103X23)R - 0800040

Technical data

General

Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN ISO 9227:2012-09
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:1997-06
Climate level	KFW 1.0 S
Cycles	2
Condensation test result	Test passed
Foil strength	175 µm

classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001694
ETIM 5.0	EC001675

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

accessories

Ink ribbon

Insert label - EMT (103X23)R - 0800040

accessories

THERMOMARK-RIBBON 110 - 5145384



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>