Plug - IB L2-M ESTOP-ADAP 1/1 M12 - 2819189

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://download.phoenixcontact.com)



Emergency-stop Y plug

Key commercial data

package_quantity	5
GTIN	4017918193157

Technical data

Dimensions

Center distance	18 mm

Ambient conditions

Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
Degree of protection	IP65
Degree of protection	IP67
Degree of protection	IP68

General

Rated current at 40°C	4 A
Rated voltage	60 V
Number of positions	5
Contact resistance	≤ 5 mΩ
Insulation resistance	≥ 10 GΩ
Coding	A - standard
Standards/regulations	M12 connector IEC 61076-2-101
Status display	No
Surge voltage category	II
Pollution degree	3
Insertion/withdrawal cycles	≥ 100
Torque	0.4 Nm (M12 connector)

Material

Inflammability class according to UL 94	HB
Contact material	CuZn
Contact surface material	Ni/Au

Plug - IB L2-M ESTOP-ADAP 1/1 M12 - 2819189

Technical data

Material

Contact carrier material	TPU GF
Material of grip body	TPU, hardly inflammable, self-extinguishing
Material, knurls	Zinc die-cast, nickel-plated
Sealing material	NBR

classifications

eCl@ss

eCl@ss 4.0	27060306
eCl@ss 4.1	27060306
eCl@ss 5.0	27061801
eCl@ss 5.1	27061801
eCl@ss 6.0	27061801
eCl@ss 7.0	27061801
eCl@ss 8.0	27061801

ETIM

ETIM 2.0	EC000830
ETIM 3.0	EC001855
ETIM 4.0	EC001855
ETIM 5.0	EC001855

UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31251501

approvals

GOST /

Approval details

GOST

accessories

Torque tool

Plug - IB L2-M ESTOP-ADAP 1/1 M12 - 2819189

accessories

TSD 04 SAC - 1208429



Screwdriver tools

SAC BIT M12-D15 - 1208432



Protective cap

PROT-M12 - 1680539




PROT-M12 FS - 1560251



Drawings


Plug - IB L2-M ESTOP-ADAP 1/1 M12 - 2819189

Dimensioned drawing



Plug M12 x 1, Y distributor


Circuit diagram



Contact assignment of the M12 Y distributor

Plug - IB L2-M ESTOP-ADAP 1/1 M12 - 2819189


Schematic diagram



Pin assignment M12 male connector, 5-pos., A-coded, male side


Plug - IB L2-M ESTOP-ADAP 1/1 M12 - 2819189

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

Schematic diagram



Layout of connector pin assignments

© Phoenix Contact 2013 - all rights reserved
http://www.phoenixcontact.com