


## Product Description

UV-filter protects the marking;Guarantees durability



## Application range

- Control cabinet manufacturing
- Plant engineering

## Benefits

- UV-filter protects the marking
- Guarantees durability

## Design

- PC labels LFL are adapted to be pushed into different sizes of character-holder
- Fastening: by cable ties (2.4 mm) or fixing of the MINI character holders with screws and rivets when using FLG end stoppers

## Note

- UV-resistant (black) cable ties should be used for outdoor applications
- Save on price, as you save on time for cutting



Technical Data

Upon request

Other sizes are available upon request

Article List

Part number	Article designation	A mm	B in mm	C mm	D (mm)	Suitable flexi-labels	Contents (unit)	PU
PTEF character-holder - without cable tie								
83254960	FLEXIMARK CharacterHolder PTEF 9.5-18 TR	12,2	9.5	18.0	30.0	LFL-17P	50	1
83254961	FLEXIMARK CharacterHolder PTEF 9.5-28 TR	12,2	9.5	28.0	40.0	LFL-28P	50	1
83254963	FLEXIMARK CharacterHolder PTEF 9.5-58 TR	12,2	9.5	35.0	47.0	LFL-35P	50	1
83254962	FLEXIMARK CharacterHolder PTEF 9.5-38 TR	12,2	9.5	38.0	50.0	LFL-35P	50	1
83254964	FLEXIMARK CharacterHolder PTEF 9.5-58 TR	12,2	9.5	58.0	70.0	2 x LFL28P	50	1
83254965	FLEXIMARK CharacterHolder PTEF 9.5-70 TR	12,2	9.5	70.0	82.0	LFL-70P	50	1
83280006	FLEXIMARK Character holder PTEF 12-18	14,8	13.0	18.0	30.0		50	1
83254976	FLEXIMARK Character Holder PTEF 12-28 TR	14,8	13.0	28.0	40.0		50	1
83254977	FLEXIMARK Character Holder PTEF 12-38 TR	14,8	13.0	38.0	50.0		50	1



83254978	FLEXIMARK Character Holder PTEF 12-58 TR	14,8	13.0	58.0	70.0		50	1
CAB character-holder - with cable tie								
83259087	FLEXIMARK Character Holder CAB 9.5-18 TR	12,2	9.5	18.0	30.0	LFL-17P	50	1
83259084	FLEXIMARK Character Holder CAB 9.5-28 TR	12,2	9.5	28.0	40.0	LFL-28P	50	1
83259085	FLEXIMARK Character Holder CAB 9.5-38 TR	12,2	9.5	38.0	50.0	LFL-35P	50	1
83259086	FLEXIMARK Character Holder CAB 9.5-58 TR	12,2	9.5	58.0	70.0	2 x LFL28P	50	1
83259078	FLEXIMARK Character Holder CAB 12-18 TR	14,8	13.0	18.0	30.0		50	1
83259079	FLEXIMARK Character Holder CAB 12-28 TR	14,8	13.0	28.0	40.0		50	1
83259080	FLEXIMARK Character Holder CAB 12-38 TR	14,8	13.0	38.0	50.0		50	1
83259081	FLEXIMARK Character Holder CAB 12-58 TR	14,8	13.0	58.0	70.0		50	1

**Footnote:**

Photographs are not to scale and do not represent detailed images of the respective products.

Contents: roll, metre, unit, marker, label