

Datasheet

Item no. 704552/ 704567/ 704580/ 704593/ 704606

V1_0717_01_en

Pushbutton Switches

Product Overview

This is using self-cleaning & fast-break of double breaking points and the switch have reliable operation, long life. It is our patent product.

Specs

The product has two types: normal type and economical type, containing pilot lamp, pushbuttons, illuminated pushbuttons, mushroom push button, emergency pushbuttons, selector switches, key-lock switches, mushroom key-lock switches, buzzer and so on. The normal diameter of the installation hole is $\Phi 22\text{mm}$ and can be installed in $\Phi 25\text{mm}$ or $\Phi 30\text{mm}$ hole easily with $\Phi 25\text{mm}$ diameter changing circle and $\Phi 30\text{mm}$ zinc-aluminum diameter changing nut.

Performance

Using high quality inflaming retarding materials. Switch unit is separated independently and the insulating performance is very well. The product meets standards of IEC 60947-5-1, GB 14048.5 etc.

Structure

The switch unit is slow-break and self-cleaning. It uses modular combination mode and you can combine from one to eight switch units optional, so can make the product meet the requirement of many special control circuits.









Protective Degree

The standard is IP40 and some types can reach IP67 with the seal cover.

Specifications, Switch Ratings, Lamp Ratings, Instructions, Installation Dimension & Circuit Diagram

Product Outline

Note: $\Phi 25$ diameter and $\Phi 30$ diameter products should be installed with diameter changing circle and please add " $\Phi 25$ " or " $\Phi 30$ " behind the part number.

Shape	Type	Type Number	Dimension	Remarks
	 90° 2 position maintain	704552		 Two keys are supplied
	 90° 2 position return	704567		
	 45° 3 position maintain	704580		
	 45° 3 position half return	704593		
	 45° 3 position self return	704606		

704552 : Key lock mushroom switch, Two position maintain, AC 250V, 5A $\Phi 22\text{mm}$, plastic crust

704567 : Key lock mushroom switch, Two position return, AC 250V, 5A $\Phi 22\text{mm}$, plastic crust

704580 : Key lock mushroom switch, Three position maintain, AC 250V, 5A $\Phi 22\text{mm}$, plastic crust

704593 : Key lock mushroom switch, Three position half return, AC 250V, 5A $\Phi 22\text{mm}$, plastic crust

704606 : Key lock mushroom switch, Three position half return, AC 250V, 5A $\Phi 22\text{mm}$, plastic crust

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

© Copyright 2017 by Conrad Electronic SE.