

Datasheet

Item no. 704480/ 704495/ 704509/ 704523/ 704536

V1_0717_01_en

Pushbutton Switches

Product Overview

This is using self-cleaning & fast-break of double breaking points and the switch have reliable operation, long life. It is our patent product.

Specs

The product has two types: normal type and economical type, containing pilot lamp, pushbuttons, illuminated pushbuttons, mushroom push button, emergency pushbuttons, selector switches, key-lock switches, mushroom key-lock switches, buzzer and so on. The normal diameter of the installation hole is Φ 22mm and can be installed in Φ 25mm or Φ 30mm hole easily with Φ 25mm diameter changing circle and Φ 30mm zinc-aluminum diameter changing nut.

Performance

Using high quality inflaming retarding materials. Switch unit is separated independently and the insulating performance is very well. The product meets standards of IEC60947-5-1,GB14048.5 etc.

Structure

The switch unit is slow- break and self - cleaning. It uses modular combination mode and you can combine from one to eight switch units optional, so can make the product meet the requirement of many special control circuits.

Protective Degree

The standard is IP40 and some types can reach IP67 with the seal cover.

Specifications, Switch Ratings, Lamp Ratings, Instructions, Installation Dimension & Circuit Diagram

Product Cutline

Note: Φ 25 diameter and Φ 30 diameter products should be installed with diameter changing circle and please add " Φ 25" or " Φ 30" behind the part number.

Shape	Туре	Type Number	Dimension	Remarks
Key-lock Switch	^L 90° 2 position maintain	704480	Panel Thickness 0.5-5	Two keys are supplied The key can be pull out in both positions.
K	^L 90° 2 position return	704495		
	L C R 45° 3 position maintain	704509		
	^L 45° 3 position half return	704523		
	L C R 45° 3 position self return	704536		

704480 : Key lock switch, Two position maintain, AC 250V, 5A Ø22mm, plastic crust

704495 : Key lock switch, Two position return, AC 250V, 5A Φ22mm, plastic crust

- 704509 : Key lock switch, Three position maintain, AC 250V, 5A @22mm,plastic crust
- 704523 : Key lock switch, Three position half return, AC 250V, 5A Φ22mm, plastic crust

704536 : Key lock switch, Three position return, AC 250V, 5A Φ22mm, plastic crust

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

© Copyright 2017 by Conrad Electronic SE.