

# Marker cards - SBS 6:UNBEDRUCKT - 1007222

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Marker cards, Card, white, Unlabeled, Can be labeled with: Plotter, Mounting type: Snap into tall marker groove, Snap into flat marker groove, For terminal block width: 6.2 mm, Lettering field: 6 x 6.1 mm

The illustration shows the product version

## Key commercial data

|                         |               |
|-------------------------|---------------|
| <b>package_quantity</b> | 10            |
| <b>GTIN</b>             | 4017918012830 |

## Technical data

### Dimensions

|                  |        |
|------------------|--------|
| <b>Width (a)</b> | 6.1 mm |
|------------------|--------|

### Ambient conditions

|  |                             |
|--|-----------------------------|
| <b>Wipe resistance</b>                 | DIN EN 61010-1 (VDE 0411-1) |
| <b>Ambient temperature (operation)</b> | -30 °C ... 110 °C           |

### General

|  |                         |
|--|-------------------------|
| <b>Note</b>                                | Can be labeled with CMS |
| <b>Color</b>                               | white                   |
| <b>Material</b>                            | cellulose acetate       |
| <b>Number of individual labels</b>         | 250                     |
| <b>Number of individual labels per row</b> | 10                      |

## classifications

### eCl@ss

|                   |          |
|-------------------|----------|
| <b>eCl@ss 4.0</b> | 24190208 |
| <b>eCl@ss 4.1</b> | 24190208 |
| <b>eCl@ss 5.0</b> | 27149103 |
| <b>eCl@ss 5.1</b> | 27141137 |
| <b>eCl@ss 6.0</b> | 27141137 |
| <b>eCl@ss 7.0</b> | 27141137 |
| <b>eCl@ss 8.0</b> | 27141137 |

### ETIM

## Marker cards - SBS 6:UNBEDRUCKT - 1007222

### classifications

#### ETIM

|                 |          |
|-----------------|----------|
| <b>ETIM 2.0</b> | EC000761 |
| <b>ETIM 3.0</b> | EC000761 |
| <b>ETIM 4.0</b> | EC000761 |
| <b>ETIM 5.0</b> | EC000761 |

#### UNSPSC

|                      |          |
|----------------------|----------|
| <b>UNSPSC 6.01</b>   | 30211811 |
| <b>UNSPSC 7.0901</b> | 39121410 |
| <b>UNSPSC 11</b>     | 39121410 |
| <b>UNSPSC 12.01</b>  | 39121410 |
| <b>UNSPSC 13.2</b>   | 39121410 |

### Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>