

## Flat zack marker sheet - ZBFM 6/WH:UNBEDRUCKT - 0803618

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Flat zack marker sheet, Sheet, white, Unlabeled, Can be labeled with: Plotter, Mounting type: Snap into flat marker groove, For terminal block width: 6.2 mm, Lettering field: 5 x 5.5 mm

### Key commercial data

|                  |               |
|------------------|---------------|
| package_quantity | 10            |
| GTIN             | 4017918007577 |

### Technical data

#### Dimensions

|           |        |
|-----------|--------|
| Width (a) | 5.5 mm |
|-----------|--------|

#### Ambient conditions

|                                 |                             |
|---------------------------------|-----------------------------|
| Wipe resistance                 | DIN EN 61010-1 (VDE 0411-1) |
| Ambient temperature (operation) | -40 °C ... 100 °C           |

#### General

|                                         |                                |
|-----------------------------------------|--------------------------------|
| Note                                    | Can be labeled with CMS        |
| Color                                   | white                          |
| Components                              | free from silicone and halogen |
| Inflammability class according to UL 94 | V2                             |
| Material                                | PA                             |
| Number of individual labels             | 100                            |
| Number of individual labels per row     | 10                             |

### classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 24190208 |
| eCl@ss 4.1 | 24190208 |
| eCl@ss 5.0 | 27149103 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |
| eCl@ss 8.0 | 27141137 |

#### ETIM

## Flat zack marker sheet - ZBFM 6/WH:UNBEDRUCKT - 0803618

### classifications

#### ETIM

|                 |          |
|-----------------|----------|
| <b>ETIM 2.0</b> | EC000761 |
| <b>ETIM 3.0</b> | EC000761 |
| <b>ETIM 4.0</b> | EC000761 |
| <b>ETIM 5.0</b> | EC000761 |

#### UNSPSC

|                      |          |
|----------------------|----------|
| <b>UNSPSC 6.01</b>   | 30211811 |
| <b>UNSPSC 7.0901</b> | 39121410 |
| <b>UNSPSC 11</b>     | 39121410 |
| <b>UNSPSC 12.01</b>  | 39121410 |
| <b>UNSPSC 13.2</b>   | 39121410 |

### Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>