

## Plastic label - UC-EMLP (27X15) - 0827894

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Plastic label, Sheet, white, Unlabeled, Can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Adhesive, Lettering field: 27 x 15 mm

### Key commercial data

|                  |               |
|------------------|---------------|
| package_quantity | 10            |
| GTIN             | 4046356461153 |

### Technical data

#### Dimensions

|            |       |
|------------|-------|
| Length (b) | 27 mm |
| Width (a)  | 15 mm |

#### Ambient conditions

|                                 |                             |
|---------------------------------|-----------------------------|
| Wipe resistance                 | DIN EN 61010-1 (VDE 0411-1) |
| Ambient temperature (operation) | -40 °C ... 120 °C           |

#### General

|                                         |                                |
|-----------------------------------------|--------------------------------|
| Color                                   | white                          |
| Components                              | free from silicone and halogen |
| Inflammability class according to UL 94 | V2                             |
| Material                                | PA                             |
| Number of individual labels             | 8                              |
| Number of individual labels per row     | 2                              |

### classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 24190208 |
| eCl@ss 4.1 | 24190208 |
| eCl@ss 5.0 | 27149103 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |
| eCl@ss 8.0 | 27141137 |

#### ETIM

## Plastic label - UC-EMLP (27X15) - 0827894

### classifications

#### ETIM

|                 |          |
|-----------------|----------|
| <b>ETIM 2.0</b> | EC000761 |
| <b>ETIM 3.0</b> | EC000761 |
| <b>ETIM 4.0</b> | EC000761 |
| <b>ETIM 5.0</b> | EC000761 |

#### UNSPSC

|                      |          |
|----------------------|----------|
| <b>UNSPSC 6.01</b>   | 30211811 |
| <b>UNSPSC 7.0901</b> | 39121410 |
| <b>UNSPSC 11</b>     | 39121410 |
| <b>UNSPSC 12.01</b>  | 39121410 |
| <b>UNSPSC 13.2</b>   | 39121410 |

### accessories

#### Magazine

P1 UC-MAG 6 - 5146121



---

### Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>