

Product Description



Product features

- Protective cover made of thermoplastics for H-B 6, H-B 10, H-B 16, H-B 24, H-B 32 housings

Article List

Part number	Article	Version	Bolts	Securing cord	Clamp	Material	Pieces / PU
with bolts for H-B 6-24 panel-mount base, surface-mount base, cable coupler hood							
10015000	H-B 6 KDB	for housing H-B 6	2	with cable lug		Plastic	10
10047000	H-B 10 KDB	for housing H-B 10	4	with cable lug		Plastic	10
10087000	H-B 16 KDB	for housing H-B 16	4	with cable lug		Plastic	5
10118000	H-B 24 KDB	for housing H-B 24	4	with cable lug		Plastic	5
with lever for H-B 6-24 hood with bolts							
10016500	H-B 6 KDT	for H-B 6 hood		with loop	2 snap-in hooks	Plastic	10
10048500	H-B 10 KDT	for H-B 10 hood		with loop	4 snap-in hooks	Plastic	10
10088500	H-B 16 KDT	for H-B 16 hood		with loop	4 snap-in hooks	Plastic	5
10119500	H-B 24 KDT	for H-B 24 hood		with loop	4 snap-in hooks	Plastic	5
with bolts for H-B 6-24 hoods with levers							



10015100	H-B 6 KDBP	for H-B 6 hood	2	with loop		Plastic	10
10047100	H-B 10 KDBP	for H-B 10 hood	4	with loop		Plastic	10
10087100	H-B 16 KDBP	for H-B 16 hood	4	with loop		Plastic	10
10118100	H-B 24 KDBP	for H-B 24 hood	4	with loop		Plastic	5
with bolts for H-B 10-32 panel-mount base, surface-mount base, cable coupler hood							
10048700	H-B 10 KDBF	for housing H-B 10	2	with loop		Plastic	10
10088700	H-B 16 KDBF	for housing H-B 16	2	with loop		Plastic	10
10118700	H-B 24 KDBF	for housing H-B 24	2	with loop		Plastic	10
10118020	H-B 32 / H-A 48 KDBF	for housing H-B 32/H-A 48	4	with loop		Plastic	10
with lever for H-B 10-24 hood with bolts							
10048600	H-B 10 KDTF	for H-B 10 hood		with loop	2 snap-in hooks	Plastic	10
10088600	H-B 16 KDTF	for H-B 16 hood		with loop	2 snap-in hooks	Plastic	10
10118600	H-B 24 KDTF	for H-B 24 hood		with loop	2 snap-in hooks	Plastic	10

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.