

# Electronic housing - UMK-BE 22,5 - 2970028

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Electronic board base, plug-in module base element

The illustration shows a combination of versions UMK SE 11,25, UMK BE 11,25,- 22,5, -45 and UMK-FE

## Product Features

- The modules can be marked using the marking grooves in the lateral element as well as with the Phoenix Contact PMB module marker, which is snapped into a bore hole (4 mm Ø) in the PCB
- Fast assembly thanks to the plug-in module principle. The tight engagement of the individual elements ensures that they are securely connected.
- Wide range of options for external conductor connection
- Due to the universal foot, the modules can be snapped onto standard EN DIN rails
- The mounting flange supports direct wall mounting

## Key commercial data

<b>package_quantity</b>	10
<b>GTIN</b>	4017918087555

## Technical data

### General

<b>Housing type</b>	Panel mounting base
<b>Housing material</b>	Polyamide
<b>Color</b>	green

### Ambient conditions

<b>Ambient temperature (operation)</b>	-40 °C ... 105 °C
--	-------------------

### Dimensions

<b>Length</b>	77 mm
<b>Width</b>	22.5 mm

### Technical data

<b>Inflammability class according to UL 94</b>	V2
--	----

## classifications

eCl@ss

# Electronic housing - UMK-BE 22,5 - 2970028

## classifications

### eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701

### ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC002779

### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

## approvals

---

UL Recognized /

---

### Approval details



## accessories

### Component housing lower part

UMK-BE 45 - 2970015



## Electronic housing - UMK-BE 22,5 - 2970028

accessories

UMK-BE 11,25 - 2971535



---

### Mounting material

UMK-FE - 2970031



---

UMK-BF - 2976077



---

### Drawings

# Electronic housing - UMK-BE 22,5 - 2970028

Dimensioned drawing

