

Product information GM 216 NJ schwarz/black

Industrial Connecting Solutions: Rectangular Connectors: Valve Connectors (Type A -B -C): Type B: Field Attachable Valve Connectors: Valve Connectors (Industrial standard): GM 216 NJ schwarz/black http://www.e-catalog.beldensolutions.com/link/57078-24228-256261-256266-256271-276218-24325-38179/en/conf/uistate

ame GM 216 NJ schwarz/black



	cable socket with central screw M 3 x 35
Delivery informations	
Availability	available
Product description	
Description	cable socket with central screw M 3 x 35

Туре	GM 216 NJ schwarz/black
Order No.	934 456-100
Other standard types	grey housing, Order No. 934 456-106
Number of contacts	2 + PF

 Cable gland
 M 16

 Conductor size
 max. 1.5 mm²

 Standard
 industrial standard (11 mm)

Standard Industrial standard (11 mm Housing Color black

Construction type B
Technical data

 Pin dimensions
 6.3 mm x 0.8 mm

 Rated voltage
 AC/DC 250 V

 Rated current
 16 A

 Contact resistance
 <= 4 m0hm</td>

Type of termination screw / cable shoe / cable eye

Suitable cables 4.5 mm to 10 mm diameter

Mounting central screw

IP 65

200 pieces

Material Central Screw

Contact surface material Sn
Contact bearer material PA

Housing material PA
Environmental conditions

Protection class (IEC 60529)

Pollution severity3Temperature range-40 °C to +125 °C

Inflammability class
Housing 94 V-1

Contact bearer 94 HB
Approvals
UR in preparation

VDE in preparation
SEV in preparation
CSA in preparation
Packing unit

Packaging unit
Scope of delivery and accessories

Accessories to order separately

(NBR) flat gasket GM 207-3, Order No. 731 423-002; (EPDM) flat gasket GM 207-7, Order No. 731 755-004; knurled screw GDM 3011-8, Order No. 732 574-001; stainless steel screw GDM 3011 RF-1, Order No. 734 363-001






Industrial Connecting Solutions: Rectangular Connectors: Valve Connectors (Type A -B -C): Type B: Field Attachable Valve Connectors: Valve Connectors (Industrial standard): GM 216 NJ schwarz/black http://www.e-catalog.beldensolutions.com/link/57078-24228-256261-256266-256271-276218-24325-38179/en/conf/uistate

Picture

Drawing



Belden Deutschland GmbH

Im Gewerbepark 2 58579 Schalksmühle Germany

Phone: +49 7127/14-1806 E-Mail: icos-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.

