




LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
		AD4 REVISED PER ECO-11-005140	29APR11	RK	HMR




SCALE 1:1

SEZIONE A-A
SECTION A-A



SEZIONE B-B
SECTION B-B



TIPICA CAVITA' PER TERMINALE
FASTIN-FASTON SR.6.35mm.
(TYPICAL CAVITY FOR
FASTIN-FASTON .250 SR.)

1 NUMERO DI IMPRONTA STAMPO
(MOULD CAVITY IDENTIFICATION NO.)

2 MARCHIO DI FABBRICA AMP
(AMP TRADE MARK)

4 AIR TIGHT PACKAGED
NON PRODOTTO DA TE ITALIA
(NOT PRODUCED BY TE ITALY)

5 NON DISPONIBILE DA TE ITALIA
(NO MORE AVAILABLE FROM TE ITALY)

6 PRODUCT IN ACCORDANCE TO IEC 60335-1 NORM.

7. FLAMMABILITY RATING: UL94 V-2

NOTE	COLORE (COLOUR)	MATERIALE (MATERIAL)	NUMERO (PART NUMBER)	REV
5, 6	NATURALE (NATURAL)	PA 6 UNFILLED	3-180916-0	AD
4, 5	ARANCIO (ORANGE)	PA 6.6 (PA 6.6 UNFILLED)	2-180916-9	AC
	VIOLETTO (VIOLET)		2-180916-8	AC
	GRIGIO (GRAY)		2-180916-7	AC
	MARRONE (BROWN)		2-180916-6	AC
	NERO (BLACK)		2-180916-5	AC
	GIALLO (YELLOW)		2-180916-4	AC
	BLU (BLUE)		2-180916-3	AC
	VERDE (GREEN)		2-180916-2	AC
	ROSSO (RED)		2-180916-1	AC
	NATURALE (NATURAL)			2-180916-0
5	ARANCIO (ORANGE)	PA 6.6 (PA 6.6 UNFILLED)	180916-9	AC
5	VIOLETTO (VIOLET)		180916-8	AC
5	GRIGIO (GRAY)		180916-7	AC
5	NERO (BLACK)		180916-5	AC
5	ROSSO (RED)		180916-1	AC
5	NATURALE (NATURAL)		180916-0	AC

DWN F. BORIN 22JUN98			
CHK/CONT. C. TARTARI 22JUN98			
APVD -		NAME	
PRODUCT SPEC 108-20020		FASTIN-FASTON CONNECTOR .250 SRS TAB HOUSING, 1 POS.	
APPLICATION SPEC -		RESTRICTED TO -	
WEIGHT -		SIZE A3	CAGE CODE 00779
MATERIAL SEE TABLE		DRAWING NO. C=180916	
FINISH -		SCALE 5:2	
CUSTOMER DRAWING		SHEET 1 OF 1	
		REV AD4	

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
0 PLC	±-
1 PLC	±-
2 PLC	±-
3 PLC	±-
4 PLC	±-
ANGLES	±2°
FINISH	-