




COBAtape

Floortape for clear definition

- Self-adhesive backed PVC floor tape.
- Designed to effectively mark lines on floors.
- Ideal for factory floors and industrial use.
- White version is popular for the leisure industry.
- Plain or hazard striped options.



Dimensions (m.)	Weight Kg	Packaging Dimensions (cm.)	Packaging Type	Packaging Volume (m.)	Packaging Quantity	Colour	Part Code
50mm x 33mm	0.44		Poly bag			Yellow	TP070002
						Blue	TP020002
						Green	TP040002
						White	TP130002
						Red	TP030002
						Black	TP010002
38mm x 33m	0.44		Poly bag			White	TP130002
50mm x 33m	0.44		Poly bag			Yellow/Black	TP010702
						White/Red	TP130302
						White/Green	TP130402

Material:	Manufactured from PVC cross linked with a rubber coating
Surface Finish:	Smooth
Thickness:	6 Mil – 1.25mm
Resistance to Chemicals:	N/A
Operating Temperature:	N/A
Shear resistance:	>120 minutes
Coating Thickness:	N/A
Adhesion Thickness:	0.016mm – 0.02mm
Tensile strength:	>16 (Lbs/inch)
Elongation %.	>150%
Environmental Resistance:	Suitable for indoor and outdoor environment
Sheer Resistance Minutes:	120

Continued on next page

United Kingdom

COBA Europe Ltd
Marlborough Drive
Fleckney, Leicestershire
LE8 8UR

+44 (0)116 240 1088
sales@cobaeurope.com
www.cobaeurope.com

Germany

COBA Europe GmbH
Pullenweg 1 - 3
41352 Korschenbroich

+49 (2161) 2945-0
verkauf@cobaeurope.de
www.cobaeurope.de

Slovakia

COBA Europe s.r.o.
Terchová - Vyšné Kamenec 11
SK-013 06

+421 41 507 11 12
sales@cobaeurope.sk
www.cobaeurope.sk

The information contained within this datasheet is for guidance only. The data and suggested application are not exhaustive. All dimensions quoted are nominal figures. Please note that some products may be subject to a degree of shrinkage when installed into some applications.

Adhesion to steel 22Oz/inch (2.4N/10mm)
Adhesion to tacking 22Oz/inch (2.4N/10mm)
Initial Tack Grams: >20
Peel Adhesion: >1 lb/inch
Typical Applications: Suitable for factory floors, walkways, sportshalls,
Installation Method: Pressure sensitive self-adhesive tape

Product Performance:
Fatigue: N/A
Slip Resistance: N/A
Wear: ● ● ●
Low ≠ High ● → ● ● ● ●

Country of Origin: China

End of document

United Kingdom

COBA Europe Ltd
Marlborough Drive
Fleckney, Leicestershire
LE8 8UR

☎ +44 (0)116 240 1088
✉ sales@cobaeeurope.com
🌐 www.cobaeeurope.com

Germany

COBA Europe GmbH
Pullenweg 1 - 3
41352 Korschenbroich

☎ +49 (2161) 2945-0
✉ verkauf@cobaeeurope.de
🌐 www.cobaeeurope.de

Slovakia

COBA Europe s.r.o.
Terchová - Vyšné Kamenec 11
SK-013 06

☎ +421 41 507 11 12
✉ sales@cobaeeurope.sk
🌐 www.cobaeeurope.sk

The information contained within this datasheet is for guidance only. The data and suggested application are not exhaustive. All dimensions quoted are nominal figures. Please note that some products may be subject to a degree of shrinkage when installed into some applications.