TP-LINK®

150Mbps Pocket-Sized Wireless Print Server

TL-WPS510U

• Features:

- 150Mbps wireless speeds allows you to share your printer wirelessly
- High compatibility with most majorities of printers on the market
- Share the printer wirelessly, the speed up to 150Mbps
- USB 2.0 High-Speed Printer Connection
- Support 64/128 bits WEP Encryption and WPA/WPA2-PSK security
- Compatible with 802.11 b/g/n products
- Equipped with a Mini-B to printer USB-B Extension Cable
- Support Windows 8/7/Vista/XP, Mac OS X 10 or above, Linux-based operating system



• Description:

150Mbps Pocketed-Sized Wireless Print Server TL-WPS510U is an ultra-compact print server that enables a single USB printer to be shared on a wireless network. It allows you simply place your printer anywhere in your home or office that works best for you. With the TL-WPS510U, there is no need for a dedicated computer anymore, everyone on the network is empowered to print to a shared printer at any time.

The TL-WPS510U print server supports IEEE 802.11b/g/n wireless network standards. Users can share the printer and configure the print server through a wireless network. With its wireless function, everyone on your network can enjoy the benefits of readily accessing a printer with the convenience of wireless connective, and you can simply place the printer anywhere you like

• Specifications:

HARDWARE FEATURES	
Interface	1 Mini-B USB 2.0 Port
Button	Reset Button
External Power Supply	3.3V DC/ 2A
Antenna type	2dBi detachable antennas (RP-SMA)
WIRELESS FEATURES	
Wireless Standards	IEEE 802.11b/g/n
Frequency	2.4GHz
Signal Rate	Up to 150Mbps
EIRP	<20dBm
Reception Sensitivity	2.4GHz 11g 54M: -77dBm 11n HT20: -74dBm, 11n HT40: -72dBm
Wireless Security	WEP, WPA / WPA2, WPA-PSK/ WPA2-PSK encryption
	DHCP (client) Support
Advanced Feature	Support UPNP
	Support Wireless Site Survey
	Firmware Upgradable
OTHERS	
Certifications	CE, FCC, RoHS
System Requirements	Windows 8/7/Vista/XP, MAC OS, NetWare, UNIX or Linux.
Dimensions (W X D X H)	2.6 x 1.6 x 0.8 in. (65 x 40 x 20mm)
Environment	Operating Temperature: 0° C~ 40° C (32°F~ 104° F) Storage Temperature: -40° C~ 70° C (- 40° F~ 158° F) Operating Humidity: 10% ~ 90% non-condensing
	Storage Humidity: 5%~90% non-condensing

• Diagram:



Package:

- 150Mbps Pocket-Sized Wireless Print Server TL-WPS510U
- Detachable antennas
- Power supply unit
- Resource CD
- Mini-B to printer USB-B Extension Cable
- Quick Installation Guide