TP-LINK®

Portable 3G/3.75G Wireless N Router
TL-MR3020

⊙ Features：

- Compatible with UMTS/HSPA/EVDO USB modems

- Travel-sized design, light and small enough to take anywhere

- Wireless N speed up to 150Mbps

- Three modes available: 3G Router, WISP Client Router and Travel Router (AP), interchangeable at the flip of a switch

- 3G/WAN failover guarantees an "always-online" Internet connection

· Quick security setup, for faster, safer and more convenient security
· A mini USB port to be connected to your laptop or power adapter for power
· IP-based bandwidth control allows administrators to determine how much bandwidth is allotted to each PC

⊙ Description：

The TL-MR3020 allows users to share a 3G mobile connection. By connecting a UMTS/HSPA/EVDO USB modem to the router, a 3G Wi-Fi hotpot is instantly established.With its portable design, it is small and light enough to take on the road, and can be powered through a USB Cable connected to a laptop or adapter, allowing users to share a 3G mobile connection even when on the train, camping or at a construction site. With the TL-MR3020, you can share the 3G internet connection with your family or friends anywhere 3G coverage is available!

◉ Specifications：

Interface	1 10/100Mbps WAN/LAN Port, USB 2.0 Port for 3G modem, a mini USB Port for power supply
Buttons	Quick Setup Security Button, Reset Button, Mode Switch
Power Supply	5VDC/1.0A external power
Dimensions	74*67*22mm
Wireless Standards	IEEE 802.11n, IEEE 802.11g, IEEE 802.11b
Frequency	2.4-2.4835GHz
Wireless Security	Support 64/128 bit WEP, WPA-PSK/WPA2-PSK,Wireless MAC Filtering
Wireless Speed	up to 150Mbps
Security	Firewall, MAC filtering, Denial of Service(DoS)
DHCP	server, DHCP Client List, Address Reservation
Port Forwarding	Virtual Server, Port Triggering, DMZ, UPnP
Operating Mode	3G Router, WISP Client Router, Travel Router (AP)
Access Control	Parental Control, Host List, Access Schedule, Rule Management
Certification	CE, FCC, RoHS
Environment	Operating temperature:-10℃~60℃ Storage Temperature: -40℃~80℃ Operating Humidity: 10%~90% non-condensing Storage Humidity: 5%~90% non-condensing

◉ Diagram:

Share the freedom of 3G

Tablets

PSP

3G Modem

Laptops

Smartphones

powered by a USB Cable

Package:

- Portable 3G/3.75G Wireless N Router TL-MR3020
- Power Adapter
- USB Cable
- Ethernet Cable
- Quick Installation Guide
- Resource CD

www.tp-link.com