

|                   |                     |                                                                                    |
|-------------------|---------------------|------------------------------------------------------------------------------------|
| U.I. Lapp<br>GmbH | <b>DATASHEET</b>    |  |
|                   | <b>SKINTOP® STR</b> | <b>53015320</b><br><b>14.11.2013</b>                                               |


High oil-resistance for maximum reliability  
Permanent vibration protection  
Optimum strain relief  
Wide, variable clamping ranges  
Various accessories (e.g. multiple sealing inserts)



Good chemical resistance



Mechanical resistance



Optimum strain relief



Temperature-resistant



Variety of approval certifications



### Application range

With reducing seal insert, to seal cables with smaller outer diameters.

### Design

PG connection thread

### Norm references / Approvals

UL File Nr. E79903

### Note

Refer to SKINTOP® PG accessories for suitable accessories  
Counter nut to be used: SKINTOP® GMP-GL

### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

|                    |                        |       |
|--------------------|------------------------|-------|
| Product Management | Document: SKINTOP® STR | 1 / 3 |
|--------------------|------------------------|-------|


|                   |                     |                                                                                                      |
|-------------------|---------------------|------------------------------------------------------------------------------------------------------|
| U.I. Lapp<br>GmbH | <b>DATASHEET</b>    |  <b>LAPP GROUP</b> |
|                   | <b>SKINTOP® STR</b> | <b>53015320</b><br><b>14.11.2013</b>                                                                 |

#### Technical Data

|                             |                                                                                   |
|-----------------------------|-----------------------------------------------------------------------------------|
| Article designation / size: | STR 11                                                                            |
| Clamping range ØF (mm):     | 2 - 7                                                                             |
| SW (mm):                    | 22                                                                                |
| Overall length, C (mm):     | 38                                                                                |
| Thread length, D (mm):      | 8                                                                                 |
| Pieces / PU:                | 100                                                                               |
| Caution:                    | Refer to Appendix T21 for the installation dimensions and torques                 |
| Colour delivered:           | Silver grey (RAL 7001)<br>Light grey (RAL 7035)<br>Black (RAL 9005), UV-resistant |
| Material:                   | Body: Polyamide<br>Seal: CR                                                       |
| Tests:                      | GGVS: TÜ.EGG.020-95                                                               |
| Protection rating:          | IP 68 - 5 bar                                                                     |
| Temperature range:          | -20°C to +80°C                                                                    |

|                    |                        |       |
|--------------------|------------------------|-------|
| Product Management | Document: SKINTOP® STR | 2 / 3 |
|--------------------|------------------------|-------|

|                   |              |                                                                                                      |
|-------------------|--------------|------------------------------------------------------------------------------------------------------|
| U.I. Lapp<br>GmbH | DATASHEET    |  <b>LAPP GROUP</b> |
|                   | SKINTOP® STR | 53015320<br>14.11.2013                                                                               |



|                    |                        |       |
|--------------------|------------------------|-------|
| Product Management | Document: SKINTOP® STR | 3 / 3 |
|--------------------|------------------------|-------|