



Voice, Data and Video Cable Verifier

VDVII

Voice, Data and Video Cable Verifier

More than just a wiremapper

The new VDV II Series are easy to use cable testers that check the integrity of copper cables commonly found in domestic, commercial or industrial voice, data or video installations, including telephone wiring, data network and video/security cabling.

Employing state-of-the-art technology, VDV II offers functionality not previously available in a wiremapper. The advanced wiremap engine accurately displays complex wiring faults instantaneously whilst TDR (Time Domain Reflectometry) aids troubleshooting and improves on-site productivity.



VDVII

Performs standard tests for copper cabling, including:

- Coax, 6Pin (RJ11/12), 8Pin (RJ45) Connectors for Copper Cable Testing
- Wiremap for Miswires, Split Pairs, Shorts and Opens
- Analog Tone Generator
- Voltage Protection
- · Shielded Cable Testing
- Single Screen Results



VDVII Plus

All the features of the VDV II including:

- Larger 2.9" Display
- Backlight
- · Hub Blink
- Cable Length
- Distance to Open
- · Carry Case & Cables



VDVII Pro

All the features of the VDV II Plus and...

- Distance to Open / Short (TDR)
- PoE Detection with Voltage Information
- Media Service Detection
- Ethernet Detection with Network Rate and Duplex Information



Wiremap with length

Accuracy

The flagship VDV II Pro utilises TDR to accurately measure cable length and provide distance to fault information. TDR's work by injecting a signal into the cable and measuring the time for any signal to be reflected back after encountering changes in impedance caused by cable damage, open and short circuits. The recorded time is then translated into an accurate distance measurement. TDR helps to pinpoint where cabling faults occur. This speeds up fault finding as well as minimising disruption and potential damage to fixtures and fixings.



Coax testing

48V 12345678 10

Service detection

Speed

With comprehensive details on faults such as opens, shorts, crossovers and split pairs, VDV II identifies wiring errors instantly. The integrated RJ11/RJ12 (voice), RJ45 (data) and F-Type (video) connectors allow faster testing of most types of low-voltage cables by eliminating the need for separate testers or adapters.

Intelligence

Connection issues are not always associated with cable faults, so VDV II Pro has the capability to help identify service related issues. By detecting the presence of voltage and checking polarity, VDV II Pro quickly determines which media service is running over the cable, such as ISDN, PBX and PoE (Power over Ethernet) resulting in faster fault diagnosis. Troubleshooting active Ethernet networks is also made easier with in-built network detection that displays network rate and duplex information. Furthermore, to prevent potentially costly damage to the tester all VDV II's are smart enough to know when they have been plugged into an outlet where voltage is present.



Applications



VOICE Support for 1, 2 or 3-pair RJ11/12 telephone cable testing



DATA Testing of shielded and unshielded Cat $5/5e/6/6_{a}/7$ LAN cable



VIDEO
Tests coax cable through
F-connector interface

VDVII

Voice, Data and Video Cable Verifier

More than just a wiremapper



Ordering Information

VDV II Range			
Part No.	Kit Contents		
R158000	VDV II - Voice, Data and Video Cable Verifier. Includes 1 x tester, 1 x dual port remote unit, 1 x coax remote unit, 1 x alkaline battery, 1 x multi-language user guide.		
R158002	VDV II Plus – Voice, Data and Video Cable Verifier. Includes 1 x tester, 1 x dual port remote unit, 1 x coax remote unit, 1 x alkaline battery, 1 x multi-language user guide, 2 x RJ45 to alligator clip cable 390mm, 2 x screened RJ45 to RJ45 cable 150mm, 2 x RJ11/12 to RJ11/12 cable 100mm, 1 x F-type plug to F-type plug cable 230mm, 1 x F-81 barrel splice, 1 x BNC female to F-type male adaptor, 1 x BNC female to F-type female adaptor, 1 x RCA female to F-type male adaptor, 1 x RCA female to F-type female adaptor, 1 x wallet wiring card, 1 x carry case.		
R158003	VDV II Pro – Voice, Data and Video Cable Verifier. Includes 1 x tester, 1 x dual port remote unit, 1 x coax remote unit, 1 x alkaline battery, 1 x multi-language user guide, 2 x RJ45 to alligator clip cable 390mm, 2 x screened RJ45 to RJ45 cable 150mm, 2 x RJ12 to RJ12 cable 100mm, 1 x F-type plug to F-type plug cable 230mm, 1 x F-81 barrel splice, 1 x BNC female to F-type male adaptor, 1 x BNC female to F-type female adaptor, 1 x RCA female to F-type female adaptor, 1 x wallet wiring card, 1 x carry case.		

Basic Specifications

Dimensions (mm)	Weight	Length Range	Battery Type
160 x 76 x 36	0.26 kg	0.3 - 450m / 1-1476 ft (Plus and Pro only)	9V alkaline. Typically 20 hours minimum continuous use (backlight off)

For detailed specifications, please visit our website.



ideal Networks

IDEAL INDUSTRIES NETWORKS DIVISION Unit 3, Europa Court, Europa Boulevard, Warrington, Cheshire, WA5 7TN, UK.

Tel. +44 (0)1925 444 446 | Fax. +44(0)1925 445501 uksales@idealnwd.com

www.idealnwd.com

Optional Accessories

Part No.	Kit Contents	
158050		Kit of 12 x RJ45 remote units* (#1 - #12)
158051	00000	Kit of 24 x RJ45 identifiers** (#1 - #24)
158053	*****	Kit of 12 x coax remote units* (#1 - #12)
62-164	0 -24	Amplifier Probe

- * Separate numbered remotes allow multiple cables to be tested more quickly
- ** Multiple identifiers simplify cable labelling at the patch panel

A subsidiary of IDEAL INDUSTRIES INC.



Specification subject to change without notice. E&OE Printed in UK.