

Mini VGA to HDMI Converter



Quick Installation Guide Ver. 1.0

All brand names and trademarks are properties of their respective owners



INTRODUCTION:

The Mini VGA to HDMI converter can convert analog PC (RGBHV) and audio signal to digital HDMI format. It can connect the analog HD-15 VGA output from PC to the digital HDMI input of the latest HD ready plasma, LCD or DLP TV. Its high bandwidth capability supports a wide range of PC and HDTV resolutions.

FEATURES:

- Video and audio in full digital HDMI format, no transmission loss!
- Supports standard VESA VGA timing output .HDMI output support up to 1920x1080@60Hz.
- Provides advanced signal and processing with great precision colors.
- No need external power adaptor (powered by USB cable) No need drive software, plug and play


Resolutions:

- Automatically identify the HDTV or monitor EDID by DDC channel.
- Adapt to HDTV or DVI monitor automatically.
- No power adaptor, no messy cords—just one HDMI cable.
- Hassle Free! Plug and play.

Supported input/output Mode:

640x480@60/75Hz,	1280x1024@60/75Hz,
800x600@60/75Hz,	1360x768@60Hz,
1024x768@75Hz,	1366x768@60Hz,
1152x864@60/75Hz,	1400x1050@60Hz,
1280x600@60Hz,	1440x900@60Hz,
1280x720@60Hz,	1600x900@60Hz,
1280x768@60/75Hz,	1600x1200@60Hz,
1280x800@60Hz,	1680x1050@60Hz,
1280x960@60Hz,	1920x1080@60Hz,

Interface specifications :



- (1)-----HDMI Output (2)-----Audio Input
(3)-----USB 5V Input (4)-----VGA Input

Accessories:

USB Cable -----	1 PCS
VGA Cable -----	1 PCS
Audio Cable -----	1 PCS
User Manual (EN) -----	1 PCS

SPECIFICATIONS:

Signal Inputs/Output	
Video Input	VGA(RGBHV)
HDMI Output	compatible with HDMI 1.3
Connector	VGA/HDMI
Input Signal	RGB: 0.7 Vp-p 75 ohm
H + V	3 to 5 Vp-p
Audio Input	Analog audio L,R
Warranty	1 Year
Environmental	
Operating Temperature	0 C to +70 C
Operating Humidity	10% to 85 % RH (no condensation)
Storage Temperature	-10 C to +80 C
Storage Humidity	5% to 90 % RH (no condensation)
Power Requirement	
External Power Supply	USB Power(500mA)
Power Consumption	0.5 watts (max)
Converter Unit	FCC,CE
Accessories Adapter	
DC Power Adapter	USB Cable
User Manual	English Version

Connection Image:

