



## USB 3.0 to Gigabit Network Adapter

10/100/1000 Mbps Gigabit Ethernet, SuperSpeed USB 3.0

Part No.: **506847**

---

The Manhattan USB 3.0 to Gigabit Network Adapter is a compact, high-performance network adapter that allows you to upgrade your desktop or notebook computer to operate at 10/100/1000 Mbps speeds on the LAN. Because it attaches to one of your computer's USB connectors, there is no need to open up your PC — and the user-friendly setup software makes installation quick and easy.

### Fast and Frugal

The Manhattan USB 3.0 to Gigabit Ethernet Network Adapter is equipped with a fully auto-sensing Gigabit LAN port capable of delivering a peak performance of 2 Gbps in full-duplex mode. It delivers exceptional performance for everyone who requires an ultra-fast and solid network connection. The latest in power-saving technology ensures the hub does not drain the battery of your computer in the process.

### Auto-Negotiation

The USB 3.0 Gigabit Adapter will automatically detect the network speed that the LAN switch port is set to and run at the same speed. The adapter supports 10Base-T Ethernet, 100Base-TX and 1000Base-T Gigabit Ethernet.

### Full Duplex

When running in full duplex mode, the USB 3.0 Gigabit Adapter connects at the following link speeds: 20 Mbps (10Base-T Ethernet), 200 Mbps (100Base-TX Fast Ethernet) and 2 Gbps (1000Base-T Gigabit Ethernet).

### Portable Design

The Manhattan USB 3.0 to Gigabit Network Adapter is compact and can be easily used from one computer to another or transferred in your notebook case as you travel. It doesn't take up a lot of space or add clutter to your work area.

### Compatible with Just About Everything

From Windows®-based Ultrabooks (like the Dell™ XPS or Acer® Aspire series) to Chromebooks™, and Apple Macbooks® to laptops and desktop PCs, as long as your device features a standard USB 2.0 or USB 3.0 port (USB 3.0 recommended for best performance), you are good to go.

### Features:

- Adds a high-speed Gigabit network connection for notebooks, 2-in-1s, Ultrabooks™, Surface® devices, MacBook® and Chromebook™
- One Gigabit Ethernet port (RJ45) supports up to 2 Gbps full-duplex transfer speed
- Upgrade your notebook or desktop computer to full gigabit speeds
- Energy-saving Energy Efficient Ethernet (IEEE 802.3az) technology

- Works with Ultrabooks, laptops and PCs running Windows 7 or Windows 8, Windows 8.1 or Windows 10
- Compatible with Apple MacBook (driver download available)
- Provides legacy support for devices running Windows XP® and Vista®
- Compatible with Microsoft Surface Pro 2, Surface 3, Surface Pro 3, Surface 4 and Surface Pro 4
- Compatible with Google Chromebook Pixel
- Compatible with Dell™ XPS series 12, 13 and 15, Alienware™ series 13, 15 and 17, HP™ Spectre, Lenovo® Yoga, Acer® Aspire and other Windows 8.1 or Windows 10 Ultrabooks
- One 1000Base-T RJ45 Gigabit Ethernet port with Auto MDI-X (auto uplink) support
- Supports jumbo frames up to 4 kBytes
- Wake-On-LAN (WOL) support
- Compliant with the USB 3.0 specification and backward compatible to USB 2.0 and USB 1.1 devices
- Three-Year Warranty

## Specifications:

### Standards

- USB Specification version 3.0
- USB Specification version 2.0
- USB Specification version 1.1
- USB Specification version 1.0
- IEEE 802.1p (Traffic Prioritization)
- IEEE 802.1q (VLAN Tagging)
- IEEE 802.3 (10Base-T Ethernet)
- IEEE 802.3ab (Twisted Pair Gigabit Ethernet)
- IEEE 802.3az (Energy Efficient Ethernet EEE)
- IEEE 802.3u (100Base-TX Fast Ethernet)

### General

- USB Type-A connector
- RJ45 connector
- Certifications: FCC Class B, CE, RoHS

### Power

- USB bus-powered
- Operating mode: 420 mA
- Suspend mode : 38 mA

### Environmental

- Dimensions: 97 (L) x 23 (W) x 15 (H) mm (3.8 x 0.9 x 0.6 in.)
- Weight: 145 g (5.11 oz.)
- Operating temperature: 0 – 40°C (32 – 104°F)
- Storage temperature: -10 – 80°C (14 – 176°F)
- Storage humidity: 5 – 85%, non-condensing

#### Supported Operating Systems

- Windows XP, Windows Vista, Windows 7, Windows 8/8.1 and Windows 10
- Apple Mac OS 10.6 - 10.12
- Google Chrome OS
- No support for Windows RT

#### Package Contents

- USB 3.0 to Gigabit Network Adapter
- Setup CD
- Instructions



