

# HD-SDI TO HDMI CONVERTER

ITEM NO.: SDI01




SDI01 converts from 3G-SDI, HD-SDI and SD-SDI to HDMI which enabling users to use cost effective HDMI display to SDI based equipment. It also provides 2 channel stereo audio. The application could be using for HD CCTV HD-SDI camera and broadcast video monitoring.

## Features:

- To send 3G/HD/SDI signal convert to HDMI.
- Support SDI (SMPTE 259M), HD-SDI (SMPTE 292M), 3G-SDI (SMPTE 424M).
- Support video signal NTSC, PAL, 720p, 1080i, 1080p.
- **Support HDMI 7.1 Channel audio.**
- Built in Equalizer to increase the working distance and signal reliability.
- SDI Loop Out with Retiming function to have the best output quality.

## Installation:



## Recommend Cable:

**Link cable recommend to use high quality 75Ω Coaxial Cable, low quality coaxial cable may case signal loss and effect transmission distance and reliability.**

All information given is based on manufacturer's specifications. Misprints, technical changes and errors are not excluded.

**Working Distance:**


<b>Max. distance via high quality 75Ω Coaxial Cable ( Belden 1694A RG6U Testing)</b>	
<b>SD resolution (270Mbps)</b>	<div style="border: 1px solid black; padding: 5px; margin-bottom: 5px;">                     [Wecken Sie das Interesse Ihrer Leser mit einem passenden Zitat aus dem Dokument, oder verwenden Sie diesen Platz, um eine Kernaussage zu betonen. Um das Textfeld an einer beliebigen Stelle auf der Seite zu platzieren, ziehen Sie es einfach.]                 </div> <p style="text-align: right;"><b>300M</b></p>
<b>HD resolution (1.45Gbps)</b>	<b>200M</b>
<b>Full HD resolution (2.97Gbps)</b>	<b>100M</b>

**LED Indication :**

**GREEN**      **Power**  
**BLUE**      **SDI signal lock**

**Panel View :**

**SDI01**



**Trouble Shooting :**

SDI01: HDMI output resolution and frequency is same as SDI input, if your TV monitor not support SDI input resolution and frequency, then it won't have picture at the monitor. For example: Under HD-SDI camera application, if your TV monitor not support 1080p@25Hz or 1080p@30Hz, then the monitor won't display. Please adjust your HD-SDI camera output resolution to 1080i or 720p.

**Specification :**

ITEM NO.	SDI01
SDI Standard / Protocol	SDI (SMPTE 259M), HD-SDI (SMPTE 292M), 3G-SDI (SMPTE 424M)
Resolution	NTSC (480i), PAL (576i), 720p@50/59.94/60Hz, 1080i@50/59.94/60Hz, 1080p@23.98/24/29.97/30/50/59.94/60Hz

SDI Input Connector	BNC 75Ω
SDI Output Connector	BNC 75Ω
HDMI Output Connector	HDMI Type A
Power Consumption	750mA (Max)
Power Supply	Switching DC5V 1AMP
Temperature	Operation: 0 to 55°C, Storage: -20 to 85°C, Humidity: up to 95%
Dimensions	67 x 110 x 27 (mm)
Weight	200 g

RoHS   

All information given is based on manufacturer's specifications. Misprints, technical changes and errors are not excluded.