

GB Installation and operating instructions

LED light

Art. No. 27744, 27745

Many thanks for deciding to buy our lights.

Our LED light is made out of sturdy, high value materials and will provide you with quality lighting. The light can be used both indoors and also outdoors.

Please read through installation and operation instructions carefully and keep these in a safe place for future reference.

We do not accept liability for damage to persons or property caused by non observation of the instructions, improper handling or for unauthorized changes made to the product.

Package contents:

- 2x & 1x LED light
- Installation and operating instructions

Technical data:

Article	Connection for each lamp	Illuminant	Protection type	Protection Class
27744	12V DC, 3,5W	LED illuminant cannot be changed	IP 20	II
Power Supply	230V AC sek: 12V, 550mA	LED illuminant cannot be changed	IP 20	III
27745	3V DC, 1,5W	LED illuminant cannot be changed	IP 20	II
Power Supply	230V AC Sek: 3V, 350mA	LED illuminant cannot be changed	IP 20	III

Safety and warning notes:

- Do not look directly into the LED - especially for longer periods of time - without protecting your eyes. A LED beam should not be directed into other people's eyes.
- Make sure, before using the light that it has not been damaged during transportation. Do not operate the light if the cable or the electrical parts are damaged. Repairs may only be done by a specialist electrician.
- Keep packaging materials well away from children and pets. Danger of suffocation!
- Be careful. The packaging contains small parts which can be swallowed by children.
- Do not leave children unattended in the area of the lights or other electrical appliances.
- Never expose the lights into water or other liquids !
- The illuminant is hot when it is in operation. The outer lamp housing will also be hot. Do not touch the light with your bare hands when it is being operated.
- The entire product must neither be changed nor converted. Changes made to the light lead to annulment of the guarantee (warranty).

Care and servicing:

- You must make sure that the power supply is disconnected before cleaning.
- Use a dry, or slightly damp cloth for cleaning.
- Never use chemicals, inflammable cleaners or abrasives for cleaning. These can damage the surface and / or the insulations of the light.



Disposal:

- Old electronic equipment must be brought to public connection points and must not be disposed of as household waste.

Installation:

- Make sure that the connection values of your building installation for the power supply to the light comply with the data stated on the name plate of this light.
- Decide on the location where installation has to take place. The lights are suitable for surface mounting or under cabinet mounting. Mount the brackets for surface mounting or under cabinet mounting. Make sure that the base and the fastening material are suitable and the weight of the lights can be supported permanently and reliably.
- Do not bend the cable, make sure that the cable and the plug are free from strain and rotational forces. Protect all cables and insulations from possible damage.
- Make sure you have a stable and reliable fastening.
- Switch on the circuit breakers of the junction box in the building again.
- The lamp has an integrated on / off switch on head.
- The name plate must not be removed.

