



"P" INDICATES FOR MALE CAPS

FCI LOGO

SECTION-AA

**NOTE:**

- 1: MATERIAL  
UL APPROVED POLYPROPYLENE RED/BLACK COLOUR
- 2: PACKAGING  
PRIMARY PACKING 100 NOS IN POLYETHYLENE BAG

"This LF product meets European Union Directives and other country regulations as described in GS-22-008"  
Packaging as per GS-14-920

50	P	70522CLF	70522BLF	56.0	15.9	54.0	4.5	12.10	12.15
	S	70527CLF	70527BLF	55.2	14.5	52.4	5.0	10.50	10.35
37	P	70521CLF	70521BLF	59.0	13.0	56.7	4.5	8.70	9.00
	S	70526CLF	70526BLF	57.3	11.8	54.7	5.0	7.40	7.50
25	P	70520CLF	70520BLF	42.0	13.2	40.0	4.5	8.98	9.00
	S	70525CLF	70525BLF	40.9	11.8	38.3	5.0	7.65	7.70
15	P	70519CLF	70519BLF	28.1	13.0	26.0	4.5	8.98	9.00
	S	70524CLF	70524BLF	27.0	11.8	24.6	5.0	7.65	7.70
09	P	70518CLF	70518BLF	20.3	13.0	17.7	4.5	8.98	9.00
	S	70523CLF	70523BLF	18.5	11.8	16.2	5.0	7.65	7.70
SHELL SIZE		PART NO: RED COLOUR	PART NO: BLACK COLOUR	A ±0.3	B ±0.3	D ±0.2	E ±0.2	F TOP	F BOTTOM
								F ±0.1	

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection		product family D-SUB		
REF NOTE										title		
ltr	ecn no	dr	date	tolerances unless otherwise specified				MM		D-SUB DUST CAP STANDARD		
A	I06-0160	GVJ	2006/08/18	angles	linear	±0.1				dwg no		
B	I09-0015	AMR	2008/01/18	0°±1°				scale -		sheet 1 of 1		size
C	I09-0025	AMR	2009/02/14	dr	H.LE GALLIC	2005/04/25			C-DSUB-0157		A4	
				enr	H.LE GALLIC	2005/04/25			type PRODUCT CUSTOMER		Drawing	
				chr	ABHILASH M.R	2009-02-14						
				app	SUDHIR VARMA	2009-02-14						
sheet index	revision	c										
	sheet	1										

FCIconnect.com

Copyright FCI