



# Fahrrad-Montageständer

Art.-Nr. 292 897 01



Bike Repair Stand  
Support de réparation pour vélo  
Fiets Reparatiestandaard  
Cavaletto per la riparazione di biciclette

**Distributor:**

POINT-Helmig GmbH  
Hammermühle 13  
51491 Overath / Germany  
[www.pointbike.de](http://www.pointbike.de)

Congratulations on your purchase of this high quality Security plus® bicycle bike stand. For safety reasons we ask you to read this manual completely before beginning the assembly. The instruction manual should be kept carefully as it is an integral part of this product. If the product is passed on to third parties, the I/M must be passed also. Furthermore, the I/M may be helpful with problems on the bicycle repair stand always.

### **Safety Note**

Caution: The maximum load of the bike repair stand of 19 kg may not be exceeded! Overloading can damage the bike repair stand and lead to accidents.

Before use check the mounting stand and all its components on damages and the tightness of all mounting screws.

Defective parts must be replaced before use!

The repair stand must be used only on a level and firm standing surface.

Caution: too fixed tightening of the retaining clamp may lead to damage on the bicycle frame or the seatpost. This applies especially for parts made of aluminum or carbon.

Carbon parts must be treated with great caution, as damage to the fiber structure is not always seen immediately!

### **Intended Use**

This bike repair stand is suitable for the performance of all common bicycle repairs.

Other use or modification of the product shall be deemed to be improper and may lead to risks of injury and damage. For damages resulting from the non-intended use, the distributor assumes no liability. This product is not intended for commercial use.

### **Cleaning**

The bicycle repair stand can be cleaned with a damp cloth.

If necessary the frame can be handled with maintenance oil.

Caution: The maintenance oil must not be used on the retaining clamp.

Do not immerse in water.

### **Maintenance**

Before use check regularly the tightness of all screws.

### **Disposing**

The packaging is 100% recyclable material. Please ask your local municipality or city government for disposal options of the metal parts.

## **Assembly of the bike repair stand**

1. First you open up the stand base. To do this open the lower quick-release (1) on the stand pipe and press it down, so that the stand base is fully deployed. Then close the quick release again.
2. Stand the repair stand into upright position. Loosen the upper quick-release (2) and pull the telescopic tube (3) to the desired length. Adjustable height of about 100 - 170 cm. For fixation close the quick release again.
3. Open the quick-release (4) at the end of the telescopic tube and push the holding arm (5) into the receiving aperture. The holding arm may be only pulled so far that its end is flush with the receiving aperture. For fixation close the quick release again.
4. Put the bracket of the tool tray around the standpipe and put the screw in the notch. Turn the screw tight.

Folding together is in the reverse order



## **Attachment of a bicycle on bike repair stand**

Please check the bike stand on damages and the tightness of all screws before inserting the bicycle.

1. Loosen the screw (6) of the retaining clamp so far that the frame or seatpost can be hooked in smoothly.
2. Set the arm in the for mounting desired position . For this, open the quick-release (4),do the setting and then close the quick release again.
3. Hang the bike with the frame or seatpost in the retaining clamp and tighten the screw (6).

Disassembly is in the reverse order.